Product data sheet

Specifications





() Discontinued

TeSys F contactor - 3P (3 NO) -AC-3 - <= 440 V 250 A - coil 120 V AC

LC1F150G6

() Discontinued on: Feb 17, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-1 AC-4
Poles Description	3P
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	120 V AC 60 Hz
[Ie] Rated Operational Current	250 A (at <104 °F (40 °C)) at <= 440 V AC-1 150 A (at <131 °F (55 °C)) at <= 440 V AC-3

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 KV
[Ith] Conventional Free Air Thermal Current	250 A (at 104 °F (40 °C))
Rated Breaking Capacity	1200 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1200 A 104 °F (40 °C) - 10 s 700 A 104 °F (40 °C) - 30 s 600 A 104 °F (40 °C) - 1 min 450 A 104 °F (40 °C) - 3 min 350 A 104 °F (40 °C) - 10 min
Associated Fuse Rating	160 A aM at <= 440 V 250 A gG at <= 440 V
Average Impedance	0.35 mOhm - Ith 250 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V IEC 60947-4-1 1500 V VDE 0110 group C
Power Dissipation Per Pole	22 W AC-1 8 W AC-3
Overvoltage Category	III
Power Pole Contact Composition	3 NO

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

0400 V AC 50/60 Hz (AC-3) 5 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-3) 30690 V AC 50/60 Hz (AC-3) 0230 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-4) 0.851.1 Uc 50/60 Hz 131 °F (55 °C)) 50.55 Uc 50/60 Hz 131 °F (55 °C)) 4z 0.3 68 °F (20 °C)) 2 0.3 68 °F (20 °C)) 31 °F (55 °C) osing ening
5 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-3) 0230 V AC 50/60 Hz (AC-3) 0230 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-4) 0.851.1 Uc 50/60 Hz 131 °F (55 °C)) 50.55 Uc 50/60 Hz 131 °F (55 °C)) Hz 0.3 68 °F (20 °C)) 2 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
0 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-3) 30690 V AC 50/60 Hz (AC-3) 230 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-4) 0.851.1 Uc 50/60 Hz 131 °F (55 °C)) 50.55 Uc 50/60 Hz 131 °F (55 °C)) 4z 0.3 68 °F (20 °C)) z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
0 V AC 50/60 Hz (AC-3) 50690 V AC 50/60 Hz (AC-3) 230 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-4) 0.851.1 Uc 50/60 Hz 131 °F (55 °C)) 50.55 Uc 50/60 Hz 131 °F (55 °C)) 4z 0.3 68 °F (20 °C)) z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
50690 V AC 50/60 Hz (AC-3) 230 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-4) 0.851.1 Uc 50/60 Hz 131 °F (55 °C)) 50.55 Uc 50/60 Hz 131 °F (55 °C)) Hz 0.3 68 °F (20 °C)) z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
0230 V AC 50/60 Hz (AC-3) 0 V AC 50/60 Hz (AC-4) 0.851.1 Uc 50/60 Hz 131 °F (55 °C)) 50.55 Uc 50/60 Hz 131 °F (55 °C)) Hz 0.3 68 °F (20 °C)) 2 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
0 V AC 50/60 Hz (AC-4) 0.851.1 Uc 50/60 Hz 131 °F (55 °C)) 50.55 Uc 50/60 Hz 131 °F (55 °C)) Hz 0.3 68 °F (20 °C)) z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
0.851.1 Uc 50/60 Hz 131 °F (55 °C)) 50.55 Uc 50/60 Hz 131 °F (55 °C)) Hz 0.3 68 °F (20 °C)) z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
50.55 Uc 50/60 Hz 131 °F (55 °C)) Hz 0.3 68 °F (20 °C)) z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
50.55 Uc 50/60 Hz 131 °F (55 °C)) Hz 0.3 68 °F (20 °C)) z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
z 0.3 68 °F (20 °C)) 31 °F (55 °C) osing
31 °F (55 °C) osing
osing
•
ening
-
it screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible without
it screw clamp terminals 2 0.000.01 in ² (14 mm ²)flexible without
it screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible with cable
it screw clamp terminals 2 0.000.00 in ² (12.5 mm ²)flexible with cable
it screw clamp terminals 1 0.000.01 in ² (14 mm ²)solid without cable
it screw clamp terminals 2 0.000.01 in ² (14 mm ²)solid without cable
bar 2 25 x 3 mm
lugs-ring terminals 1 0.19 in² (120 mm²)
connector 1 0.19 in ² (120 mm ²)
bolted connection
it 10.62 lbf.in (1.2 N.m)
159.31 lbf.in (18 N.m)
-1
1
-1
is register of shipping)
is register of shipping)
ls register of shipping)
ls register of shipping)
is register of shipping)
d

Environment

Ip Degree Of Protection	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
Protective Treatment	тн
Ambient Air Temperature For Operation	-40140 °F (-4060 °C)
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Permissible Ambient Air Temperature Around The Device	140158 °F (6070 °C) at Uc

Height	6.69 in (170 mm)
Width	6.44 in (163.5 mm)
Depth	6.73 in (171 mm)
Operating Altitude	9842.52 ft (3000 m) without derating
Net Weight	7.56 lb(US) (3.43 kg)

Ordering and shipping details

Category	US10I1222336
Discount Schedule	0112
Gtin	3389110122251
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21 cm)
Package 1 Width	7.87 in (20 cm)
Package 1 Length	9.45 in (24 cm)
Package 1 Weight	9.24 lb(US) (4.19 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov