Product data sheet

Specification





Contactor, TeSys K, 3P, AC-3, It or eq to 440V 12 A, 1 NC aux., 48VAC coil

LC1K1201E7

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 86.00 USD

Main

······································	
Range	TeSys
Product Or Component Type	Contactor
Device Short Name	LC1K
Device Application	Control
Contactor Application	Motor control Resistive load

Complementary

Join promontary	
Utilisation Category	AC-3
	AC-3e
	AC-1
	AC-4
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC <= 400 Hz
	Signalling circuit <= 690 V AC <= 400 Hz
[le] Rated Operational Current	12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit
	12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3e for power circuit
	20 A (at <140 °F (60 °C)) at <= 690 V AC AC-1 for power circuit
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage 48 V AC 50/60 Hz	
Motor Power Kw	3 kW 220230 V AC 50/60 Hz AC-3
	5.5 kW 380415 V AC 50/60 Hz AC-3
	5.5 kW 440 V AC 50/60 Hz AC-3
	4 kW 690 V AC 50/60 Hz AC-3
	3 kW 220230 V AC 50/60 Hz AC-3e
	5.5 kW 380415 V AC 50/60 Hz AC-3e
	5.5 kW 440 V AC 50/60 Hz AC-3e
	4 kW 690 V AC 50/60 Hz AC-3e
	3 kW 220230 V AC 50/60 Hz AC-4
	5.5 kW 380415 V AC 50/60 Hz AC-4
	5.5 kW 440 V AC 50/60 Hz AC-4
	4 kW 690 V AC 50/60 Hz AC-4
Auxiliary Contact Composition	1 NC
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air	20 A (at 140 °F (60 °C)) for power circuit
Thermal Current	10 A (at 122 °F (50 °C)) for signalling circuit

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Irms Rated Making Capacity	144 A AC for power circuit conforming to IEC 60947 110 A AC for signalling circuit conforming to IEC 60947	
Rated Breaking Capacity	110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660690 V conforming to IEC 60947	
[Icw] Rated Short-Time Withstand Current	115 A 122 °F (50 °C) - 1 s for power circuit 105 A 122 °F (50 °C) - 5 s for power circuit 100 A 122 °F (50 °C) - 10 s for power circuit 75 A 122 °F (50 °C) - 30 s for power circuit 55 A 122 °F (50 °C) - 1 min for power circuit 50 A 122 °F (50 °C) - 3 min for power circuit 25 A 122 °F (50 °C) - 3 min for power circuit 25 A 122 °F (50 °C) - >= 15 min for power circuit 80 A - 1 s for signalling circuit 90 A - 500 ms for signalling circuit 110 A - 100 ms for signalling circuit	
Associated Fuse Rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit 10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660	
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Inrush Power In Va	30 VA (at 68 °F (20 °C))	
Hold-In Power Consumption In Va	4.5 VA (at 68 °F (20 °C))	
Heat Dissipation	1.3 W	
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <122 °F (50 °C)) Drop-out: >= 0.20 Uc (at <122 °F (50 °C))	
Connections - Terminals	screw clamp terminals 1 0.000.01 in² (1.54 mm²)solid screw clamp terminals 1 0.000.01 in² (0.754 mm²)flexible without cable end screw clamp terminals 1 0.000.00 in² (0.342.5 mm²)flexible with cable end screw clamp terminals 2 0.000.01 in² (1.54 mm²)solid screw clamp terminals 2 0.000.01 in² (0.754 mm²)flexible without cable end screw clamp terminals 2 0.000.00 in² (0.341.5 mm²)flexible with cable end	
Maximum Operating Rate	3600 cyc/h	
Auxiliary Contacts Type	Instantaneous 1 NC	
Signalling Circuit Frequency	<= 400 Hz	
Minimum Switching Current	5 mA for signalling circuit	
Minimum Switching Voltage	17 V for signalling circuit	
Operating Time	1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing	
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1	
Non Overlap Distance	0.02 in (0.5 mm)	
Mechanical Durability	10 Mcycles	
Electrical Durability	1.3 Mcycles 12 A AC-3 <= 440 V 1.3 Mcycles 12 A AC-3e <= 440 V 0.3 Mcycles 20 A AC-1 <= 690 V 0.02 Mcycles 72 A AC-4 <= 440 V	
Mechanical Robustness	Shocks contactor closed, on X axis10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Y axis15 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Z axis15 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on X axis6 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Y axis10 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Z axis10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor closed4 Gn, 5300 Hz IEC 60068-2-6 Vibrations contactor opened2 Gn, 5300 Hz IEC 60068-2-6	
Height	2.28 in (58 mm)	
Width	1.77 in (45 mm)	

Depth 2.24 in (57 mm)

Environment

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1
Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA
Protective Treatment	TC IEC 60068 TC DIN 50016
Operating Altitude	6561.68 ft (2000 m) without derating
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

Ordering and shipping details

Category	US10I1222326	
Discount Schedule	0112	
Gtin	3389110858808	
Returnability	No	
Country Of Origin	ID	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.60 in (6.600 cm)	
Package 1 Width	1.89 in (4.800 cm)	
Package 1 Length	2.44 in (6.200 cm)	
Package 1 Weight	6.35 oz (180.000 g)	
Unit Type Of Package 2	S02	
Number Of Units In Package 2	50	
Package 2 Height	5.91 in (15.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	20.55 lb(US) (9.320 kg)	

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability Green Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
End of Life Information
WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov