# **Product data sheet**

Specification





# Changeover contactor, TeSys K, 4P, AC-1, It or eq to 440V 10A, 24VAC coil

LC2K090045B7

! Discontinued on: Jul 12, 2021

#### ① Discontinued

### Main

Range	TeSys
Product Name	TeSys K
Product Or Component Type	Changeover contactor
Device Short Name	LC2K
Device Application	Control
Contactor Application	Resistive load
Utilisation Category	AC-1
Device Presentation	Preassembled with reversing power busbar
Poles Description	4P
Power Pole Contact Composition	4 NO
[Ue] Rated Operational Voltage	Power circuit 690 V AC 50/60 Hz
[le] Rated Operational Current	20 A (at <122 °F (50 °C)) at <= 440 V AC AC-1 for power circuit 16 A (at <158 °F (70 °C)) at 690 V AC AC-1 for power circuit
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	20 A (at 122 °F (50 °C)) for power circuit
Irms Rated Making Capacity	110 A AC for power circuit conforming to NF C 63-110 110 A AC for power circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 110 A at 220230 V conforming to IEC 60947 110 A at 380400 V conforming to IEC 60947 70 A at 660690 V conforming to IEC 60947
[lcw] Rated Short-Time Withstand Current	90 A 122 °F (50 °C) - 1 s for power circuit  85 A 122 °F (50 °C) - 5 s for power circuit  80 A 122 °F (50 °C) - 10 s for power circuit  60 A 122 °F (50 °C) - 30 s for power circuit  45 A 122 °F (50 °C) - 1 min for power circuit  40 A 122 °F (50 °C) - 3 min for power circuit  20 A 122 °F (50 °C) - >= 15 min for power circuit
Associated Fuse Rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Apr 24, 2024 Life Is On Schneider

[Ui] Rated Insulation Voltage	Power circuit 600 V UL 508
	Power circuit 690 V IEC 60947-4-1
	Power circuit 600 V CSA C22.2 No 14
Electrical Durability	0.18 Mcycles 20 A AC-1 <= 440 V
Interlocking Type	Mechanical
Mounting Support	Rail
	Plate
Standards	EN/IEC 60947-4-1
	GB/T 14048.4
	UL 60947-4-1
	CSA C22.2 No 60947-4-1
	JIS C8201-4-1
Product Certifications	CB Scheme
	CCC
	UL
	CSA
	EAC
	CE
	UKCA
Connections - Terminals	solder pins 1.5 x 0.9 mm
Operating Time	1020 ms coil energisation and NO closing
	1020 ms coil de-energisation and NO opening
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	5 Mcycles
Maximum Operating Rate	3600 cyc/h
Complementary	
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <122 °F (50 °C))
•	Drop-out: 0.20.75 Uc (at <122 °F (50 °C))
Inrush Power In Va	30 VA (at 68 °F (20 °C))
Hold-In Power Consumption In Va	4.5 VA (at 68 °F (20 °C))
Heat Dissipation	1.3 W
Environment	

Livitoiiiieit		
Ip Degree Of Protection	IP20 VDE 0106	
Protective Treatment	TC IEC 60068 TC DIN 50016	
Ambient Air Temperature For Operation	-13122 °F (-2550 °C)	
Ambient Air Temperature For Storage	-58176 °F (-5080 °C)	
Operating Altitude	erating Altitude 6561.68 ft (2000 m) without derating	
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102	
Mechanical Robustness	Shocks contactor closed, on X axis10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Y axis15 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Z axis15 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on X axis6 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Y axis10 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Z axis10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor closed4 Gn, 5300 Hz IEC 60068-2-6 Vibrations contactor opened2 Gn, 5300 Hz IEC 60068-2-6	
Height	2.28 in (58 mm)	
Width	3.54 in (90 mm)	

Depth	2.24 in (57 mm)
Net Weight	0.84 lb(US) (0.38 kg)

# Ordering and shipping details

Category	22327-CTR,K-LINE,AC,OPEN,REV	
Discount Schedule	112	
Gtin	3389110491593	
Returnability	No	
Country Of Origin	FR	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6 cm)
Package 1 Width	2.44 in (6.2 cm)
Package 1 Length	3.62 in (9.2 cm)
Package 1 Weight	15.17 oz (430 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov