

LP4K09107JW3

TeSys K contactor - 3P - AC-3 \leq 440 V 9 A - 1
NO aux. - 12 V DC coil

Price* : 110.00 USD



⚠ Discontinued

LP4K09107JW3 has not been replaced. Please contact your customer care center for more information.

Main

Range	TeSys
Product or component type	Contacteur
Product name	TeSys K
Device short name	LP4K
Device application	Control
Contacteur application	Motor control Resistive load

Complementary

Utilisation category	AC-1 AC-3 AC-4
Poles description	3P
Power pole contact composition	3 NO
System Voltage	690 V AC 50/60 Hz power circuit \leq 690 V AC 50/60 Hz signalling circuit
[Ie] rated operational current	9 A at \leq 440 V AC AC-3 power circuit 20 A (\leq 122 °F (50 °C)) at \leq 440 V AC AC-1 power circuit 16 A (\leq 158 °F (70 °C)) at 690 V AC AC-1 power circuit
Control circuit type	DC low consumption
[Uc] control circuit voltage	12 V DC
Motor power kW	4 kW at 380...415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 4 kW at 480 V AC 50/60 Hz 4 kW at 500...600 V AC 50/60 Hz 4 kW at 660...690 V AC 50/60 Hz 2.2 kW at 220...230 V AC 50/60 Hz
Auxiliary contact composition	1 NO
[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	20 A at \leq 122 °F (50 °C) power circuit 10 A at \leq 122 °F (50 °C) signalling circuit
Irms rated making capacity	110 A AC power circuit conforming to NF C 63-110 110 A AC power circuit conforming to IEC 60947 110 A AC signalling circuit conforming to IEC 60947

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rated breaking capacity	110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 110 A at 220...230 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947
[Icw] rated short-time withstand current	20 A $\leq 50\text{ }^{\circ}\text{C} \geq 15$ min power circuit 90 A $\leq 122\text{ }^{\circ}\text{F}$ (50 $^{\circ}\text{C}$) 1 s power circuit 85 A $\leq 122\text{ }^{\circ}\text{F}$ (50 $^{\circ}\text{C}$) 5 s power circuit 80 A $\leq 122\text{ }^{\circ}\text{F}$ (50 $^{\circ}\text{C}$) 10 s power circuit 60 A $\leq 122\text{ }^{\circ}\text{F}$ (50 $^{\circ}\text{C}$) 30 s power circuit 45 A $\leq 122\text{ }^{\circ}\text{F}$ (50 $^{\circ}\text{C}$) 1 min power circuit 40 A $\leq 122\text{ }^{\circ}\text{F}$ (50 $^{\circ}\text{C}$) 3 min power circuit 80 A 1 s signalling circuit 90 A 500 ms signalling circuit 110 A 100 ms signalling circuit
Associated fuse rating	25 A gG at ≤ 440 V power circuit 25 A aM power circuit 10 A gG signalling circuit conforming to IEC 60947 10 A gG signalling circuit conforming to VDE 0660
Average impedance	3 mOhm at 50 Hz - Ith 20 A power circuit
[UI] rated insulation voltage	690 V signalling circuit conforming to IEC 60947-4-1 690 V signalling circuit conforming to IEC 60947-5-1 600 V signalling circuit conforming to UL 508 600 V power circuit conforming to CSA C22.2 No 14 600 V signalling circuit conforming to CSA C22.2 No 14 690 V power circuit conforming to IEC 60947-4-1 600 V power circuit conforming to UL 508
Insulation resistance	> 10 MOhm signalling circuit
Inrush power in W	1.8 W at 68 $^{\circ}\text{F}$ (20 $^{\circ}\text{C}$)
Hold-in power consumption in W	1.8 W at 68 $^{\circ}\text{F}$ (20 $^{\circ}\text{C}$)
Heat dissipation	1.8 W
Control circuit voltage limits	0.7...1.30 U _c at $\leq 122\text{ }^{\circ}\text{F}$ (50 $^{\circ}\text{C}$) operational 0.1...0.7 U _c at $\leq 122\text{ }^{\circ}\text{F}$ (50 $^{\circ}\text{C}$) drop-out
Connections - terminals	Faston terminals 1 6.35 mm Faston terminals 2 2.8 mm
Operating rate	3600 cyc/h
Coil technology	Built-in bidirectional peak limiting diode suppressor
Auxiliary contacts type	Type instantaneous (1 NO)
Minimum switching current	5 mA signalling circuit
Minimum switching voltage	17 V signalling circuit
Mounting support	Plate Rail
Operating time	10...20 ms coil de-energisation and NO opening 30...40 ms coil energisation and NO closing
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Non overlap distance	0.02 in (0.5 mm)
Mechanical durability	30 Mcycles
Electrical durability	0.18 Mcycles 20 A AC-1 at U _e ≤ 440 V 1.3 Mcycles 9 A AC-3 at U _e ≤ 440 V
Mechanical robustness	Shocks contactor closed, on Z axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Z axis 10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor opened 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor opened, on X axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Y axis 6 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on X axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Y axis 10 Gn for 11 ms IEC 60068-2-27
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Product weight	0.52 lb(US) (0.235 kg)

Environment

Standards	BS 5424 IEC 60947 NF C 63-110 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-58...176 °F (-50...80 °C)
Operating altitude	6561.68 ft (2000 m) without derating in temperature
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

Ordering and shipping details

Category	22321 - CTR,K-LINE,DC,OPEN,NONREV
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	FR

Contractual warranty

Warranty period	18 months
-----------------	-----------