

Product data sheet

Specifications



Contactor, TeSys K, 3P, AC-3, It or eq to 440V, 9A, 1 NO aux, 72VDC coil

LP4K09107SW3

⚠ Discontinued

Main

Range Of Product	TeSys K
Range	TeSys
Product Or Component Type	Contactor
Device Short Name	LP4K
Utilisation Category	AC-4 AC-1 AC-3
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Poles Description	3P
Pole Contact Composition	3 NO
[Ie] Rated Operational Current	20 A (at <122 °F (50 °C)) at <= 440 V AC AC-1 for power circuit 9 A at <= 440 V AC AC-3 for power circuit 16 A (at <158 °F (70 °C)) at 690 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	Instantaneous 1 NO

Complementary

Contactor Application	Motor control Resistive load
Auxiliary Contact Composition	1 NO
Control Circuit Voltage Limits	Operational: 0.7...1.30 Uc (at <122 °F (50 °C)) Drop-out: 0.1...0.7 Uc (at <122 °F (50 °C))
[Ui] Rated Insulation Voltage	Power circuit 600 V UL 508 Power circuit 690 V IEC 60947-4-1 Signalling circuit 690 V IEC 60947-4-1 Signalling circuit 690 V IEC 60947-5-1 Signalling circuit 600 V UL 508 Power circuit 600 V CSA C22.2 No 14 Signalling circuit 600 V CSA C22.2 No 14
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
Mounting Support	Rail Plate
Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA
Ambient Air Temperature For Operation	-13...122 °F (-25...50 °C)
Ambient Air Temperature For Storage	-58...176 °F (-50...80 °C)
Operating Altitude	6561.68 ft (2000 m) without derating
[Ue] Rated Operational Voltage	Power circuit 690 V AC 50/60 Hz Signalling circuit <= 690 V AC 50/60 Hz
[Ith] Conventional Free Air Thermal Current	20 A (at 122 °F (50 °C)) for power circuit 10 A (at 122 °F (50 °C)) for signalling circuit
Irms Rated Making Capacity	110 A AC for power circuit conforming to NF C 63-110 110 A AC for power circuit conforming to IEC 60947 110 A AC for signalling circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 110 A at 220...230 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947
Associated Fuse Rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit 10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit
Operating Time	10...20 ms coil de-energisation and NO opening 30...40 ms coil energisation and NO closing
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	30 Mcycles
Maximum Operating Rate	3600 cyc/h
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Net Weight	0.52 lb(US) (0.235 kg)
Compatibility Code	LP4K

Environment

Inrush Power In W	1.8 W 68 °F (20 °C))
Hold-In Power Consumption In W	1.8 W 68 °F (20 °C)
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

Ordering and shipping details

Category	22321-CTR,K-LINE,DC,OPEN,NONREV
----------	---------------------------------

Discount Schedule	I12
Gtin	3389110500615
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------