

# Product data sheet

Specifications



## TeSys Deca reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 25 A - 48 V AC coil

LC2D256E7

Discontinued on: Oct 8, 2021

Discontinued

### Main

Range	TeSys
Product Name	TeSys Deca
Product Or Component Type	Reversing contactor
Device Short Name	LC2D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-1
Device Presentation	Preassembled with reversing power busbar
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25...400 Hz Power circuit <= 300 V DC
[Ie] Rated Operational Current	25 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 40 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
Motor Power Kw	5.5 kW at 220...230 V AC 50 Hz 11 kW at 380...400 V AC 50 Hz 11 kW at 415...440 V AC 50 Hz 15 kW at 500 V AC 50 Hz 15 kW at 660...690 V AC 50 Hz
Motor Power Hp (UI / Csa)	3 hp at 230/240 V AC 60 Hz for 1 phase motors 5 hp at 200/208 V AC 60 Hz for 3 phase motors 2 hp at 115 V AC 60 Hz for 1 phase motors 7.5 hp at 230/240 V AC 60 Hz for 3 phase motors 15 hp at 460/480 V AC 60 Hz for 3 phase motors 20 hp at 575/600 V AC 60 Hz for 3 phase motors
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz
Auxiliary Contact Composition	1 NO + 1 NC
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 40 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 450 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	450 A at 440 V for power circuit conforming to IEC 60947

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>[Icw] Rated Short-Time Withstand Current</b>	50 A 104 °F (40 °C) - 10 min for power circuit 120 A 104 °F (40 °C) - 1 min for power circuit 240 A 104 °F (40 °C) - 10 s for power circuit 380 A 104 °F (40 °C) - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
<b>Associated Fuse Rating</b>	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 40 A gG at <= 690 V coordination type 2 for power circuit
<b>Average Impedance</b>	2 mOhm - lth 40 A 50 Hz for power circuit
<b>[Ui] Rated Insulation Voltage</b>	Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL
<b>Electrical Durability</b>	1.65 Mcycles 25 A AC-3 <= 440 V 1.4 Mcycles 40 A AC-1 <= 440 V
<b>Power Dissipation Per Pole</b>	1.25 W AC-3 3.2 W AC-1
<b>Front Cover</b>	With
<b>Interlocking Type</b>	Mechanical
<b>Mounting Support</b>	Rail Plate
<b>Standards</b>	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
<b>Product Certifications</b>	LROS (Lloyds register of shipping) CSA GL RINA GOST DNV CCC BV UL
<b>Connections - Terminals</b>	Control circuit lugs-ring terminals 0.31 in (8 mm)) Power circuit lugs-ring terminals 0.39 in (10 mm))
<b>Tightening Torque</b>	Control circuit 15.05 lbf.in (1.7 N.m) lugs-ring terminals flat Ø 6 mm M3.5 Control circuit 15.05 lbf.in (1.7 N.m) lugs-ring terminals Philips No 2 M3.5 Power circuit 22.13 lbf.in (2.5 N.m) lugs-ring terminals flat Ø 8 mm M4 Power circuit 22.13 lbf.in (2.5 N.m) lugs-ring terminals Philips No 2 M4
<b>Operating Time</b>	12...22 ms closing 4...19 ms opening
<b>Safety Reliability Level</b>	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
<b>Mechanical Durability</b>	15 Mcycles
<b>Maximum Operating Rate</b>	3600 cyc/h 140 °F (60 °C)

## Complementary

<b>Coil Technology</b>	Without built-in suppressor module
<b>Control Circuit Voltage Limits</b>	0.3...0.6 Uc -40...158 °F (-40...70 °C) drop-out AC 50/60 Hz 0.8...1.1 Uc -40...140 °F (-40...60 °C) operational AC 50 Hz 0.85...1.1 Uc -40...140 °F (-40...60 °C) operational AC 60 Hz 1...1.1 Uc 140...158 °F (60...70 °C) operational AC 50/60 Hz

Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 70 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 7 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	2...3 W 50/60 Hz
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling Circuit Frequency	25...400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Insulation Resistance	> 10 MOhm for signalling circuit

## Environment

Ip Degree Of Protection	IP20 front face IEC 60529
Climatic Withstand	IACS E10 IEC 60947-1 Annex Q category D
Protective Treatment	TH IEC 60068-2-30
Pollution Degree	3
Ambient Air Temperature For Operation	-40...140 °F (-40...60 °C) 140...158 °F (60...70 °C) with derating
Ambient Air Temperature For Storage	-76...176 °F (-60...80 °C)
Operating Altitude	0...9842.52 ft (0...3000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open2 Gn, 5...300 Hz Vibrations contactor closed4 Gn, 5...300 Hz Shocks contactor closed15 Gn for 11 ms Shocks contactor open8 Gn for 11 ms
Height	3.35 in (85 mm)
Width	3.54 in (90 mm)
Depth	3.62 in (92 mm)
Net Weight	1.74 lb(US) (0.787 kg)

## Ordering and shipping details

Category	22354-CTR, TESYS D, OPEN, 9-38A AC
Discount Schedule	I12
Gtin	3389110684780
Returnability	No
Country Of Origin	FR

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.29 in (10.9 cm)

Package 1 Width	4.49 in (11.4 cm)
Package 1 Length	4.65 in (11.8 cm)
Package 1 Weight	28.75 oz (815 g)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Certifications & Standards

Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="#">www.P65Warnings.ca.gov</a>