

Product availability : Stock - Normally stocked in distribution facility



Price* : 107.00 USD



Main

Range	TeSys
Product name	TeSys LRD
Product or component type	Differential thermal overload relay
Device short name	LR2D
Relay application	Motor protection
Product compatibility	LC1D95 LC1D80
Network type	DC AC
Thermal protection adjustment range	48...65 A
[Ui] rated insulation voltage	600 V power circuit conforming to CSA 600 V power circuit conforming to UL 690 V power circuit conforming to IEC 60947-4-1

Complementary

Network frequency	0...400 Hz
Mounting support	Plate with specific accessories Rail with specific accessories Under contactor
Tripping threshold	1.14 +/- 0.06 I _r conforming to IEC 60947-4-1
[I _{th}] conventional free air thermal current	5 A for signalling circuit
Permissible current	0.72 A at 500 V AC-15 for signalling circuit 0.06 A at 440 V DC-13 for signalling circuit
System Voltage	690 V AC 0...400 Hz
[U _{imp}] rated impulse withstand voltage	6 kV
Phase failure sensitivity	Tripping current 130 % of I _r on two phase, the last one at 0
Control type	Red push-button stop

Blue push-button for reset mode

Temperature compensation	-4...140 °F (-20...60 °C)
Connections - terminals	Power circuit : screw clamp terminals 1 cable(s) 4...35 mm ² flexible without cable end Power circuit : screw clamp terminals 1 cable(s) 4...35 mm ² flexible with cable end Power circuit : screw clamp terminals 1 cable(s) 4...35 mm ² solid without cable end Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible without cable end Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² solid without cable end
Tightening torque	Control circuit : 1.7 N.m on screw clamp terminals Power circuit : 9 N.m on screw clamp terminals
Height	3.94 in (100 mm)
Width	2.95 in (75 mm)
Depth	4.76 in (121 mm)
Product weight	1.18 lb(US) (0.535 kg)

Environment

Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C) without derating conforming to IEC 60947-4-1
Ambient air temperature for storage	-76...158 °F (-60...70 °C)
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations 6 Gn IEC 60068-2-6 Shocks 15 Gn for 11 ms IEC 60068-2-7
Dielectric strength	6 kVat 50 Hz conforming to IEC 60255-5
Standards	EN 60947-5-1 ATEX D 94/9/CE IEC 60947-5-1 UL 508 EN 60947-4-1 CSA C22.2 No 14 IEC 60947-4-1
Product certifications	CCC LROS (Lloyds register of shipping) CSA UL DNV RINA GL BV ATEX INERIS GOST

Ordering and shipping details

Category	22347 - CONTACTOR,D-LINE,OVERLOADS-NEW
Discount Schedule	I12
GTIN	00785901258506
Nbr. of units in pkg.	1
Package weight(Lbs)	1.1599999999999999
Returnability	Y
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0630 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------