# Product data sheet

Specifications





## TeSys Deca reversing contactor -3P(3 NO) - AC-3 - <= 440 V 25 A -220 V AC coil

LC2D25M7

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 462.12 USD

Μ	ai	n
	u	•••

Mann			
Range	TeSys TeSys Deca		
Product Name	TeSys D TeSys Deca		
Product Or Component Type	Reversing contactor		
Device Short Name	LC2D		
Contactor Application	Motor control Resistive load		
Utilisation Category	AC-1 AC-3 AC-3e		
Device Presentation	Preassembled with reversing power busbar		
Poles Description	3P		
Power Pole Contact Composition	3 NO		
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC		
[le] Rated Operational Current	25 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 40 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit		
Motor Power Kw	5.5 kW at 220230 V AC 50-60 Hz 11 kW at 380400 V AC 50-60 Hz 11 kW at 415 V AC 50-60 Hz 11 kW at 440 V AC 50-60 Hz 15 kW at 500 V AC 50-60 Hz 15 kW at 660690 V AC 50-60 Hz		
Motor Power Hp (UI / Csa)	3 hp at 230/240 V AC 60 Hz for 1 phase motors 5 hp at 200/208 V AC 60 Hz for 3 phase motors 2 hp at 115 V AC 60 Hz for 1 phase motors 7.5 hp at 230/240 V AC 60 Hz for 3 phase motors 15 hp at 460/480 V AC 60 Hz for 3 phase motors 20 hp at 575/600 V AC 60 Hz for 3 phase motors		
Control Circuit Type	AC 50/60 Hz		
[Uc] Control Circuit Voltage	220 V AC 50/60 Hz		
Auxiliary Contact Composition	1 NO + 1 NC		
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947		
Overvoltage Category	III		
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 40 A (at 140 °F (60 °C)) for power circuit		

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 450 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	450 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	50 A 104 °F (40 °C) - 10 min for power circuit 120 A 104 °F (40 °C) - 1 min for power circuit 240 A 104 °F (40 °C) - 10 s for power circuit 380 A 104 °F (40 °C) - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 40 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 40 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL
Electrical Durability	1.65 Mcycles 25 A AC-3 <= 440 V 1.4 Mcycles 40 A AC-1 <= 440 V 1.65 Mcycles 25 A AC-3e <= 440 V
Power Dissipation Per Pole	1.25 W AC-3 3.2 W AC-1 1.25 W AC-3e
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Rail Plate
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1
Product Certifications	DNV CSA CCC UL GL LROS (Lloyds register of shipping) BV RINA GOST UKCA CB

Connections - Terminals	Control circuit screw clamp terminals 1 0.000.01 in <sup>2</sup> (14 mm <sup>2</sup> )flexible without			
	cable end			
	Control circuit screw clamp terminals 2 0.000.01 in <sup>2</sup> (14 mm <sup>2</sup> )flexible without cable end			
	Control circuit screw clamp terminals 1 0.000.01 in <sup>2</sup> (14 mm <sup>2</sup> )flexible with cable end			
	Control circuit screw clamp terminals 2 0.000.00 in <sup>2</sup> (12.5 mm <sup>2</sup> )flexible with cable end			
	Control circuit screw clamp terminals 1 0.000.01 in <sup>2</sup> (14 mm <sup>2</sup> )solid			
	Control circuit screw clamp terminals 2 0.000.01 in <sup>2</sup> (14 mm <sup>2</sup> )solid			
	Power circuit screw clamp terminals 1 0.000.02 in <sup>2</sup> (2.510 mm <sup>2</sup> )flexible without cable end			
	Power circuit screw clamp terminals 2 0.000.02 in <sup>2</sup> (2.510 mm <sup>2</sup> )flexible without cable end			
	Power circuit screw clamp terminals 1 0.000.02 in <sup>2</sup> (110 mm <sup>2</sup> )flexible with cable end			
	Power circuit screw clamp terminals 2 0.000.01 in <sup>2</sup> (1.56 mm <sup>2</sup> )flexible with cable end			
	Power circuit screw clamp terminals 1 0.000.02 in <sup>2</sup> (1.510 mm <sup>2</sup> )solid			
	Power circuit screw clamp terminals 2 0.000.02 in² (2.510 mm²)solid			
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm			
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2			
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals flat Ø 6 mm			
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals Philips No 2			
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2			
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals pozidriv No 2			
Operating Time	1222 ms closing			
	419 ms opening			
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1			
	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1			
Mechanical Durability	15 Mcycles			
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)			

## Complementary

Coil Technology	Without built-in suppressor module				
Control Circuit Voltage Limits	0.30.6 Uc -40158 °F (-4070 °C) drop-out AC 50/60 Hz 0.81.1 Uc -40140 °F (-4060 °C) operational AC 50 Hz 0.851.1 Uc -40140 °F (-4060 °C) operational AC 60 Hz 11.1 Uc 140158 °F (6070 °C) operational AC 50/60 Hz				
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 70 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))				
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 7 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))				
Heat Dissipation	23 W 50/60 Hz				
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1				
Signalling Circuit Frequency	25400 Hz				
Minimum Switching Current	5 mA for signalling circuit				
Minimum Switching Voltage	17 V for signalling circuit				
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact				
Insulation Resistance	> 10 MOhm for signalling circuit				

### Environment

Ip Degree Of Protection	IP20 front face IEC 60529
Climatic Withstand	IACS E10 IEC 60947-1 Annex Q category D
Protective Treatment	TH IEC 60068-2-30

Pollution Degree	3			
Ambient Air Temperature For Operation	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating			
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)			
Operating Altitude	09842.52 ft (03000 m)			
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1			
Flame Retardance	V1 conforming to UL 94			
Mechanical Robustness	Vibrations contactor open2 Gn, 5300 Hz Vibrations contactor closed4 Gn, 5300 Hz Shocks contactor closed15 Gn for 11 ms Shocks contactor open8 Gn for 11 ms			
Height	3.35 in (85 mm)			
Width	3.54 in (90 mm)			
Depth	3.62 in (92 mm)			
Net Weight	1.74 lb(US) (0.787 kg)			

# Ordering and shipping details

Category	US10I1222354
Discount Schedule	0112
Gtin	3389110387155
Returnability	No
Country Of Origin	ID

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.33 in (11.000 cm)
Package 1 Width	4.33 in (11.000 cm)
Package 1 Length	5.51 in (14.000 cm)
Package 1 Weight	32.95 oz (934.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	5
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	10.87 lb(US) (4.930 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	80
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	191.54 lb(US) (86.880 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Pvc Free


#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

## Product data sheet

#### **Dimensions Drawings**

#### Dimensions





LC2 or 2 x LC1	а	b	c <sup>(1)</sup>	e1	e2	G
D09 to D18 (AC)	90	77	86	4	1.5	80
D093 to D123 (AC)	90	99	86	-	-	80
D09 to D18 (DC)	90	77	95	4	1.5	80
D093 to D123 (DC)	90	99	95	-	-	80
D25 to D38 (AC)	90	85	92	9	5	80
D183 to D383 (AC)	90	99	92	-	-	80
D25 to D32 (DC)	90	85	101	9	5	80
D183 to D383 (DC)	90	99	101	-	-	80
e1 and e2: including cabling.						
(1) With safety cover, without add-on block.						

### Product data sheet

Connections and Schema

#### Wiring

