Product data sheet

Specifications



TeSys D reversing contactor -3P(3 NO) - AC-3 - <= 440 V 32 A -110 V DC coil

LC2D32FDV

① Discontinued

Main

Range	TeSys
Product Name	TeSys D
Product Or Component Type	Reversing contactor
Device Short Name	LC2D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-1 AC-3
Device Presentation	Preassembled with reversing power busbar
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	32 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 50 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
Motor Power Kw	7.5 kW at 220230 V AC 50 Hz 15 kW at 380400 V AC 50 Hz 15 kW at 415440 V AC 50 Hz 18.5 kW at 500 V AC 50 Hz 18.5 kW at 660690 V AC 50 Hz
Motor Power Hp (UI / Csa)	2 hp at 115 V AC 60 Hz for 1 phase motors 5 hp at 230/240 V AC 60 Hz for 1 phase motors 7.5 hp at 200/208 V AC 60 Hz for 3 phase motors 10 hp at 230/240 V AC 60 Hz for 3 phase motors 20 hp at 460/480 V AC 60 Hz for 3 phase motors 30 hp at 575/600 V AC 60 Hz for 3 phase motors
Control Circuit Type	DC standard
[Uc] Control Circuit Voltage	110 V DC
Auxiliary Contact Composition	1 NO + 1 NC
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 50 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 550 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	550 A at 440 V for power circuit conforming to IEC 60947

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Life Is On Schneider

[Icw] Rated Short-Time Withstand Current	60 A 104 °F (40 °C) - 10 min for power circuit 138 A 104 °F (40 °C) - 1 min for power circuit 260 A 104 °F (40 °C) - 10 s for power circuit
	430 A 104 °F (40 °C) - 1 s for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	63 A gG at <= 690 V coordination type 1 for power circuit
	63 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 50 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1
	Power circuit 600 V CSA Power circuit 600 V UL
	Signalling circuit 690 V IEC 60947-1
	Signalling circuit 600 V CSA
	Signalling circuit 600 V UL
Electrical Durability	1.65 Mcycles 32 A AC-3 <= 440 V
	1.4 Mcycles 50 A AC-1 <= 440 V
Power Dissipation Per Pole	2 W AC-3
	5 W AC-1
Front Cover	With
Interlocking Type	Electrical and mechanical
Mounting Support	Rail
	Plate
Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1 IEC 60947-4-1
	IEC 60947-5-1
	UL 508
Product Certifications	RINA
	DNV
	CSA
	GOST BV
	UL
	CCC
	GL
	LROS (Lloyds register of shipping)
Connections - Terminals	Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible without
	cable end Control circuit screw clamp terminals 2 0.000.01 in ² (14 mm ²)flexible without
	cable end Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible with cable
	end
	Control circuit screw clamp terminals 2 0.000.00 in ² (12.5 mm ²)flexible with cable end
	Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)solid
	Control circuit screw clamp terminals 2 0.000.01 in ² (14 mm ²)solid Power circuit screw clamp terminals 1 0.000.02 in ² (2.510 mm ²)flexible without
	cable end
	Power circuit screw clamp terminals 2 0.000.02 in² (2.510 mm²)flexible without
	cable end
	Power circuit screw clamp terminals 1 0.000.02 in ² (110 mm ²)flexible with cable end
	Power circuit screw clamp terminals 2 0.000.01 in² (1.56 mm²)flexible with cable
	end Power circuit screw clamp terminals 1 0 00 0 02 in² (1 5 10 mm²)solid
	Power circuit screw clamp terminals 1 0.000.02 in² (1.510 mm²)solid Power circuit screw clamp terminals 2 0.000.02 in² (2.510 mm²)solid
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals hat 6 0 min
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals flat Ø 6 mm
Operating Time	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals flat Ø 6 mm

Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	30 Mcycles
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil Technology	Built-in bidirectional peak limiting diode suppressor	
Control Circuit Voltage Limits	0.10.25 Uc -40158 °F (-4070 °C) drop-out DC 0.71.25 Uc -40140 °F (-4060 °C) operational DC 11.25 Uc 140158 °F (6070 °C) operational DC	
Time Constant	28 ms	
Inrush Power In W	5.4 W 68 °F (20 °C))	
Hold-In Power Consumption In W	5.4 W 68 °F (20 °C)	
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Current	5 mA for signalling circuit	
Minimum Switching Voltage	17 V for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Insulation Resistance	> 10 MOhm for signalling circuit	

Environment

IP20 front face IEC 60529	
TH IEC 60068-2-30	
3	
-40…140 °F (-40…60 °C) 140…158 °F (60…70 °C) with derating	
-76176 °F (-6080 °C)	
09842.52 ft (03000 m)	
1562 °F (850 °C) IEC 60695-2-1	
V1 conforming to UL 94	
Vibrations contactor open2 Gn, 5300 Hz Vibrations contactor closed4 Gn, 5300 Hz Shocks contactor closed15 Gn for 11 ms Shocks contactor open8 Gn for 11 ms	
3.35 in (85 mm)	
3.54 in (90 mm)	
3.98 in (101 mm)	
2.48 lb(US) (1.127 kg)	
-	

Ordering and shipping details

Category	22355-CTR,TESYS D,OPEN,9-38A DC	
Discount Schedule	112	
Gtin	3389110414752	
Returnability	No	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information