

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 60.00 USD



Main

Range	TeSys
Product name	TeSys LRD
Product or component type	Non differential thermal overload relay
Device short name	LR3D
Relay application	Motor protection
Product compatibility	LC1D12 LC1D38 LC1D25 LC1D32 LC1D18 LC1D09
Network type	AC DC
Thermal protection adjustment range	0.16...0.25 A
[Ui] rated insulation voltage	600 V power circuit conforming to CSA 600 V power circuit conforming to UL 690 V power circuit conforming to IEC 60947-4-1

Complementary

Network frequency	0...400 Hz
Mounting support	Plate with specific accessories Rail with specific accessories Under contactor
Tripping threshold	1.14 +/- 0.06 I _r conforming to IEC 60947-4-1
[I _{th}] conventional free air thermal current	5 A for signalling circuit
Permissible current	3 A at 120 V AC-15 for signalling circuit 0.22 A at 125 V DC-13 for signalling circuit
System Voltage	690 V AC 0...400 Hz

[Uimp] rated impulse withstand voltage	6 kV
Phase failure sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control type	Red push-button stop Blue push-button for reset mode
Temperature compensation	-4...140 °F (-20...60 °C)
Connection pitch	0.57 in (14.5 mm)
Connections - terminals	Power circuit: lugs-ring terminals Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible without cable end Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² solid without cable end
Tightening torque	Control circuit : 1.7 N.m on screw clamp terminals Power circuit : 2.3 N.m on lugs-ring terminals screw : M4
Width	1.77 in (45 mm)
Depth	2.76 in (70 mm)
Product weight	0.27 lb(US) (0.124 kg)

Environment

Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C) without derating conforming to IEC 60947-4-1
Ambient air temperature for storage	-76...158 °F (-60...70 °C)
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations 6 Gn IEC 60068-2-6 Shocks 15 Gn for 11 ms IEC 60068-2-7
Dielectric strength	6 kV at 50 Hz conforming to IEC 60255-5
Standards	UL 508 ATEX D 94/9/CE IEC 60947-4-1 IEC 60947-5-1 CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1
Product certifications	RINA CCC UL GL LROS (Lloyds register of shipping) GOST DNV ATEX INERIS BV CSA

Ordering and shipping details

Category	22347 - CONTACTOR,D-LINE,OVERLOADS-NEW
Discount Schedule	I12
GTIN	003389110377941
Nbr. of units in pkg.	1
Package weight(Lbs)	0.32000000000000001
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0643 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------