

LC2D50A3FE7

TeSys D reversing contactor - 3P(3 NO) - AC-3 -
≤ 440 V 50 A - 115 V AC coil

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 627.00 USD



Main

Range	TeSys
Product name	TeSys D
Product or component type	Reversing contactor
Device short name	LC2D
Contacteur application	Motor control Resistive load
Utilisation category	AC-1 AC-3
Device presentation	Preassembled with reversing power busbar
Poles description	3P
Power pole contact composition	3 NO
System Voltage	AC 25...400 Hz for power circuit DC for power circuit
[Ie] rated operational current	50 A (≤ 140 °F (60 °C)) at ≤ 440 V AC AC-3 power circuit 80 A (≤ 140 °F (60 °C)) at ≤ 440 V AC AC-1 power circuit
Motor power kW	30 kW at 500 V AC 50 Hz 25 kW at 415 V AC 50 Hz 30 kW at 440 V AC 50 Hz 22 kW at 380...400 V AC 50 Hz 33 kW at 660...690 V AC 50 Hz 15 kW at 220...230 V AC 50 Hz
Motor power HP (UL / CSA)	3 hp at 115 V AC 60 Hz 1 phase motors 7.5 hp at 230/240 V AC 60 Hz 1 phase motors 15 hp at 200/208 V AC 60 Hz 3 phases motors 15 hp at 230/240 V AC 60 Hz 3 phases motors 40 hp at 460/480 V AC 60 Hz 3 phases motors 40 hp at 575/600 V AC 60 Hz 3 phases motors
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	115 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 1 NC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
Overvoltage category	III
[Ith] conventional free air thermal current	80 A at <= 140 °F (60 °C) power circuit 10 A at <= 140 °F (60 °C) signalling circuit
Irms rated making capacity	900 A at 440 V power circuit conforming to IEC 60947 140 A AC signalling circuit conforming to IEC 60947-5-1 250 A DC signalling circuit conforming to IEC 60947-5-1
Rated breaking capacity	900 A at 440 V power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit 400 A <= 104 °F (40 °C) 10 s power circuit 810 A <= 104 °F (40 °C) 1 s power circuit 84 A <= 104 °F (40 °C) 10 min power circuit 208 A <= 104 °F (40 °C) 1 min power circuit
Associated fuse rating	100 A gG at <= 690 V coordination type 1 power circuit 100 A gG at <= 690 V coordination type 2 power circuit 10 A gG signalling circuit conforming to IEC 60947-5-1
Average impedance	1.5 mOhm at 50 Hz - Ith 80 A power circuit
[Ui] rated insulation voltage	600 V power circuit certifications CSA 600 V power circuit certifications UL 690 V power circuit conforming to IEC 60947-4-1 690 V signalling circuit conforming to IEC 60947-1 600 V signalling circuit certifications CSA 600 V signalling circuit certifications UL
Electrical durability	1.45 Mcycles 50 A AC-3 at Ue <= 440 V 1.1 Mcycles 80 A AC-1 at Ue <= 440 V
Power dissipation per pole	3.7 W AC-3 9.6 W AC-1
Safety cover	With
Interlocking type	Mechanical
Mounting support	Plate Rail
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product certifications	CCC CSA GOST UL
Connections - terminals	Power circuit: EverLink BTR screw connectors 1 cable(s) 0...0.05 in ² (1...35 mm ²) - cable stiffness: flexible - without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 0...0.05 in ² (1...35 mm ²) - cable stiffness: flexible - with cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 0...0.05 in ² (1...35 mm ²) - cable stiffness: solid - without cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 0...0.04 in ² (1...25 mm ²) - cable stiffness: flexible - without cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 0...0.04 in ² (1...25 mm ²) - cable stiffness: flexible - with cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 0...0.04 in ² (1...25 mm ²) - cable stiffness: solid - without cable end Control circuit: spring terminals 1 cable(s) 0 in ² (2.5 mm ²) - cable stiffness: flexible - without cable end Control circuit: spring terminals 2 cable(s) 0 in ² (2.5 mm ²) - cable stiffness: flexible - without cable end
Tightening torque	Power circuit: 70.8 lbf.in (8 N.m) - on EverLink BTR screw connectors - cable 0.04...0.05 in ² (25...35 mm ²) hexagonal 0.16 in (4 mm) Power circuit : 5 N.m - on EverLink BTR screw connectors - cable 2.5...25 mm ² hexagonal 4 mm
Operating time	12...26 ms closing 4...19 ms opening
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	6 Mcycles
Operating rate	<= 3600 cyc/h at <= 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.6 Uc drop-out at 140 °F (60 °C), AC 50/60 Hz 0.8...1.1 Uc operational at 140 °F (60 °C), AC 50 Hz 0.85...1.1 Uc operational at 140 °F (60 °C), AC 60 Hz
Inrush power in VA	140 VA at 68 °F (20 °C) (cos ϕ 0.75) 60 Hz 160 VA at 68 °F (20 °C) (cos ϕ 0.75) 50 Hz
Hold-in power consumption in VA	13 VA at 68 °F (20 °C) (cos ϕ 0.3) 60 Hz 15 VA at 68 °F (20 °C) (cos ϕ 0.3) 50 Hz
Heat dissipation	4...5 W at 50/60 Hz
Auxiliary contacts type	Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1
Signalling circuit frequency	25...400 Hz
Minimum switching current	5 mA signalling circuit
Minimum switching voltage	17 V
Non-overlap time	1.5 ms on de-energisation (between NC and NO contact) 1.5 ms on energisation (between NC and NO contact)
Insulation resistance	> 10 MOhm signalling circuit


Environment

IP degree of protection	IP20 front face conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068-2-30
Pollution degree	3
Ambient air temperature for operation	23...140 °F (-5...60 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Permissible ambient air temperature around the device	-40...158 °F (-40...70 °C) at Uc
Operating altitude	9842.52 ft (3000 m) without derating
Fire resistance	1562 °F (850 °C) conforming to IEC 60695-2-1
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor open 10 Gn for 11 ms Shocks contactor closed 15 Gn for 11 ms
Height	4.8 in (122 mm)
Width	4.69 in (119 mm)
Depth	4.72 in (120 mm)
Product weight	4.14 lb(US) (1.88 kg)

Ordering and shipping details

Category	22357 - CTR, TESYS D, OPEN, 40-65A AC
Discount Schedule	I12
GTIN	003389118340022
Nbr. of units in pkg.	1
Package weight(Lbs)	4.620000000000001
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------