



Price* : 62.00 USD



ⓘ Discontinued

Main

Range	TeSys
Product name	TeSys LRD
Product or component type	Differential thermal overload relay
Device short name	LR3D
Relay application	Motor protection
Product compatibility	LC1D09 LC1D12 LC1D18 LC1D25 LC1D32
Network type	AC DC
Thermal protection adjustment range	5.5...8 A
[Ui] rated insulation voltage	600 V power circuit conforming to CSA 600 V power circuit conforming to UL 690 V power circuit conforming to IEC 60947-4-1

Complementary

Network frequency	0...400 Hz
Mounting support	Independent mounting Rail with specific accessories
Tripping threshold	1.14 +/- 0.06 I _r conforming to IEC 60947-4-1
[I _{th}] conventional free air thermal current	5 A for signalling circuit
Permissible current	1.5 A at 240 V AC-15 for signalling circuit 0.1 A at 250 V DC-13 for signalling circuit
System Voltage	1000 V AC 0...400 Hz for power circuit conforming to IEC 60947-4-1
[U _{imp}] rated impulse withstand voltage	6 kV
Phase failure sensitivity	Tripping current I 30 % of I _r on one phase, the others at I _r conforming to IEC 60947-4-1
Control type	Red push-button stop Blue push-button for reset mode
Temperature compensation	-4...140 °F (-20...60 °C)

Tightening torque	Control circuit : 1.7 N.m on screw clamp terminals Power circuit : 1.85 N.m on screw clamp terminals
Width	1.77 in (45 mm)
Depth	3.62 in (92 mm)
Product weight	0.42 lb(US) (0.19 kg)

Environment

Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C) without derating conforming to IEC 60947-4-1
Ambient air temperature for storage	-76...158 °F (-60...70 °C)
Dielectric strength	6 kV at 50 Hz conforming to IEC 60255-5
Standards	ATEX D 94/9/CE EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 CSA C22.2 No 14
Product certifications	ATEX INERIS BV CCC CSA DNV GL GOST LROS (Lloyds register of shipping) RINA UL

Ordering and shipping details

Category	22347 - CONTACTOR,D-LINE,OVERLOADS-NEW
Discount Schedule	I12
GTIN	00785901501862
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5100000000000001
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0630 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------

LR3D1512A1 is replaced by:



Thermal overload relays LR3D12L

TeSys LRD thermal overload relays - 5.5...8 A - class 20

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017
