

Product data sheet

Characteristics

LP4K06015BW3

TeSys K contactor - 3P - AC-3 \leq 440 V 6 A - 1
NC aux. - 24 V DC coil

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 92.00 USD



Main

Range	TeSys
Product or component type	Contactor
Product name	TeSys K
Device short name	LP4K
Device application	Control
Contactor application	Motor control

Complementary

Utilisation category	AC-3 AC-4
Poles description	3P
Power pole contact composition	3 NO
System Voltage	690 V AC 50/60 Hz power circuit \leq 690 V AC 50/60 Hz signalling circuit
[Ie] rated operational current	6 A at \leq 440 V AC AC-3 power circuit
Control circuit type	DC low consumption
[Uc] control circuit voltage	24 V DC
Motor power kW	1.5 kW at 220...230 V AC 50/60 Hz AC-3 2.2 kW at 380...415 V AC 50/60 Hz AC-3 1.5 kW at 400 V AC 50/60 Hz AC-4 3 kW at 660...690 V AC 50/60 Hz AC-3 3 kW at 440 V AC 50/60 Hz AC-3 3 kW at 480 V AC 50/60 Hz AC-3 3 kW at 500...600 V AC 50/60 Hz AC-3
Auxiliary contact composition	1 NC
[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ith] conventional free air thermal current	20 A at <= 122 °F (50 °C) power circuit 10 A at <= 122 °F (50 °C) signalling circuit
Irms rated making capacity	110 A AC power circuit conforming to NF C 63-110 110 A AC power circuit conforming to IEC 60947 110 A AC signalling circuit conforming to IEC 60947
Rated breaking capacity	110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 110 A at 220...230 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947
[Icw] rated short-time withstand current	20 A <= 50 °C >= 15 min power circuit 90 A <= 122 °F (50 °C) 1 s power circuit 85 A <= 122 °F (50 °C) 5 s power circuit 80 A <= 122 °F (50 °C) 10 s power circuit 60 A <= 122 °F (50 °C) 30 s power circuit 45 A <= 122 °F (50 °C) 1 min power circuit 40 A <= 122 °F (50 °C) 3 min power circuit 80 A 1 s signalling circuit 90 A 500 ms signalling circuit 110 A 100 ms signalling circuit
Associated fuse rating	25 A gG at <= 440 V power circuit 25 A aM power circuit 10 A gG signalling circuit conforming to IEC 60947 10 A gG signalling circuit conforming to VDE 0660
Average impedance	3 mOhm at 50 Hz - Ith 20 A power circuit
[Ui] rated insulation voltage	690 V signalling circuit conforming to IEC 60947-4-1 690 V signalling circuit conforming to IEC 60947-5-1 600 V signalling circuit conforming to UL 508 600 V power circuit conforming to CSA C22.2 No 14 600 V signalling circuit conforming to CSA C22.2 No 14 690 V power circuit conforming to IEC 60947-4-1 600 V power circuit conforming to UL 508
Insulation resistance	> 10 MOhm signalling circuit
Inrush power in W	1.8 W at 68 °F (20 °C)
Hold-in power consumption in W	1.8 W at 68 °F (20 °C)
Heat dissipation	1.8 W
Control circuit voltage limits	0.7...1.30 Uc at <= 122 °F (50 °C) operational 0.1...0.7 Uc at <= 122 °F (50 °C) drop-out
Connections - terminals	Solder pins 1.5 x 0.9 mm
Operating rate	3600 cyc/h
Coil technology	Built-in bidirectional peak limiting diode suppressor
Auxiliary contacts type	Type instantaneous (1 NC)
Minimum switching current	5 mA signalling circuit
Minimum switching voltage	17 V signalling circuit
Mounting support	Printed circuit boards
Operating time	10...20 ms coil de-energisation and NO opening 30...40 ms coil energisation and NO closing
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Non overlap distance	0.02 in (0.5 mm)
Mechanical durability	30 Mcycles
Electrical durability	1.3 Mcycles 6 A AC-3 at Ue <= 440 V
Mechanical robustness	Shocks contactor closed, on Z axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Z axis 10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor opened 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor opened, on X axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Y axis 6 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on X axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Y axis 10 Gn for 11 ms IEC 60068-2-27
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)

Product weight	0.52 lb(US) (0.235 kg)
----------------	------------------------

Environment

Standards	BS 5424 IEC 60947 NF C 63-110 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-58...176 °F (-50...80 °C)
Operating altitude	6561.68 ft (2000 m) without derating in temperature
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

Ordering and shipping details

Category	22321 - CTR,K-LINE,DC,OPEN,NONREV
Discount Schedule	I12
GTIN	003389110498097
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5500000000000000
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0825 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------