

Product availability : Stock - Normally stocked in distribution facility



Price* : 298.00 USD



Main

Range	TeSys
Product name	TeSys LRD
Product or component type	Electronic thermal overload relay
Device short name	LR9D
Relay application	Motor protection
Product compatibility	LC1D115 NSX circuit breaker LC1D150
Network type	AC
Signalling function	Alarm
Thermal protection adjustment range	60...100 A
[Ui] rated insulation voltage	1000 V power circuit conforming to IEC 60947-4-1 600 V power circuit conforming to CSA 600 V power circuit conforming to UL

Complementary

Network frequency	50...60 Hz
[Us] rated supply voltage	24 V DC
Supply voltage limits	17...32 V
Mounting support	Rail Under contactor
Tripping threshold	1.05 +/- 0.06 In alarm conforming to IEC 60947-4-1 1.12 +/- 0.06 In de-energisation conforming to IEC 60947-4-1
[Ith] conventional free air thermal current	5 A for signalling circuit
System Voltage	690 V 50...60 Hz
Associated fuse rating	5 A gG for signalling circuit
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 61000-4-5

Phase failure sensitivity	Tripping in 4 s +/- 20 % conforming to IEC 60947-4-1
Control type	Red push-button stop Blue push-button for reset mode
Temperature compensation	-4...140 °F (-20...60 °C)
Switching capacity in mA	0...150 mA
Voltage drop	<= 2.5 V closed state
Connections - terminals	Power circuit: bars Control circuit : screw clamp terminals 1 cable(s) 0.5...1.5 mm ² flexible without cable end Control circuit : screw clamp terminals 2 cable(s) 0.5...1.5 mm ² flexible without cable end Alarm circuit : screw clamp terminals 1 cable(s) 0.5...1.5 mm ² flexible without cable end
Tightening torque	Alarm circuit : 0.45 N.m on screw clamp terminals Power circuit : 18 N.m on bars screw : M8 Control circuit : 1.2 N.m on screw clamp terminals
Depth	5.2 in (132 mm)
Product weight	1.95 lb(US) (0.885 kg)

Environment

Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C) without derating conforming to IEC 60947-4-1
Ambient air temperature for storage	-76...158 °F (-60...70 °C)
Operating altitude	<= 6561.68 ft (2000 m) without derating
Mechanical robustness	Vibrations 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks 13 Gn for 11 ms IEC 60068-2-7
Dielectric strength	6 kV at 50 Hz conforming to IEC 60255-5
Standards	VDE 0660 IEC 255-17 IEC 255-8 IEC 60947-4-1 EN 60947-4-1
Product certifications	UL 508 CSA 22-2

Ordering and shipping details

Category	22347 - CONTACTOR,D-LINE,OVERLOADS-NEW
Discount Schedule	I12
GTIN	00785901163657
Nbr. of units in pkg.	1
Package weight(Lbs)	2.1800000000000002
Returnability	Y
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------