

Product availability : Stock - Normally stocked in distribution facility



Price* : 737.00 USD



Main

Range	TeSys
Product name	TeSys LRF
Device short name	LR9F
Product or component type	Electronic thermal overload relay
Relay application	Motor protection
Product compatibility	LC1F225...LC1F500
Network type	AC
Thermal overload class	Class 20 conforming to IEC 60947-4
Thermal protection adjustment range	300...500 A
Signalling function	Pre-alarm indicator

Complementary

Network frequency	50/60 Hz
Supply voltage limits	17...32 V
Mounting support	Plate Direct on contactor
Tripping threshold	1.12 +/- 0.06 In tripping conforming to IEC 60947-4-1
Surge withstand	4 kV conforming to IEC 61000-4-5
Contacts type and composition	1 NO + 1 NC
[Ith] conventional free air thermal current	5 A for control circuit
System Voltage	1000 V AC 50/60 Hz power circuit conforming to VDE 0110 group C
[Ui] rated insulation voltage	1000 V AC power circuit conforming to IEC 60947-4
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-1
Phase failure sensitivity	Tripping in 4 s +/- 20 % conforming to IEC 60947-4-1
Reset	Manual reset

Control type	Dial white full-load current adjustment Test button red Push-button red reset Push-button stop
Local signalling	Trip indicator
Temperature compensation	-4...158 °F (-20...70 °C)
Current consumption	<= 5 mA no-load
Switching capacity for alarm	0...150 mA
Voltage drop	2.5 V closed state
Connections - terminals	Control circuit: screw clamp terminals 1 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: solid Control circuit: screw clamp terminals 2 cable 0 in ² (1 mm ²) - cable stiffness: solid Control circuit : screw clamp terminals 1 cable 0.75...2.5 mm ² - cable stiffness: flexible - with cable end cable end Control circuit : screw clamp terminals 1 cable 0.75...4 mm ² - cable stiffness: flexible - without cable end cable end Control circuit : screw clamp terminals 2 cable 1...1.5 mm ² - cable stiffness: flexible - with cable end cable end Control circuit : screw clamp terminals 2 cable 1...2.5 mm ² - cable stiffness: flexible - without cable end cable end Power circuit : lugs-ring terminals M10
Tightening torque	Control circuit : 1.2 N.m - on screw clamp terminals Power circuit : 35 N.m - on screw clamp terminals
Height	5.39 in (136.8 mm)
Width	5.91 in (150 mm)
Depth	5.02 in (127.6 mm)
Product weight	5.11 lb(US) (2.32 kg)

Environment

Standards	EN 60947-4-1 IEC 60255-17 IEC 60255-8 IEC 60947-4-1 VDE 0660
Product certifications	CSA UL
Protective treatment	TH
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-4...131 °F (-20...55 °C) conforming to IEC 60255-8
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Operating altitude	<= 6561.68 ft (2000 m) without derating
Fire resistance	1562 °F (850 °C) conforming to IEC 60695-2-1
Mechanical robustness	Shocks 13 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations 5...300 Hz 2 Gn conforming to IEC 60068-2-6
Dielectric strength	6 kVat 50 Hz conforming to IEC 255-5
Electromagnetic compatibility	Radiated radio-frequency electromagnetic field immunity test 10 V/m conforming to IEC 61000-4-3 Resistance to electrostatic discharge 6 kV in indirect mode conforming to IEC 61000-4-2 Resistance to electrostatic discharge 8 kV in air conforming to IEC 61000-4-2 Fast transients immunity test 2 kV conforming to IEC 61000-4-4

Ordering and shipping details

Category	22334 - CONTACTOR,F-LINE,OVERLOADS
Discount Schedule	I12
GTIN	00785901640226
Nbr. of units in pkg.	1
Package weight(Lbs)	4.5200000000000005
Returnability	Y
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------