## Product data sheet

Specification





# Contactor, TeSys K, 4P, 2 NO + 2 NC, AC-1, It or eq to 440V, 20A, 24VDC coil

LP4K09008BW3

Product availability: Stock - Normally stocked in distribution facility

Price\*: 116.00 USD

#### Main

Wall	
Range	TeSys
Product Or Component Type	Contactor
Device Short Name	LP4K
Contactor Application	Resistive load

#### Complementary

Utilisation Category	AC-1
Poles Description	4P
Power Pole Contact Composition	2 NO + 2 NC
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC <= 400 Hz Signalling circuit <= 690 V AC <= 400 Hz
[le] Rated Operational Current	20 A (at <140 °F (60 °C)) at <= 690 V AC AC-1 for power circuit
Control Circuit Type	DC wide range
[Uc] Control Circuit Voltage	24 V DC
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	20 A (at 140 °F (60 °C)) for power circuit 10 A (at 122 °F (50 °C)) for signalling circuit
Irms Rated Making Capacity	110 A AC for power circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 220230 V conforming to IEC 60947 110 A at 380400 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660690 V conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	90 A 122 °F (50 °C) - 1 s for power circuit  85 A 122 °F (50 °C) - 5 s for power circuit  80 A 122 °F (50 °C) - 10 s for power circuit  60 A 122 °F (50 °C) - 30 s for power circuit  45 A 122 °F (50 °C) - 1 min for power circuit  40 A 122 °F (50 °C) - 3 min for power circuit  20 A 122 °F (50 °C) - >= 15 min for power circuit
Associated Fuse Rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Ui] Rated Insulation Voltage	Power circuit 600 V UL 508	
	Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA C22.2 No 14	
Inrush Power In W	1.8 W 68 °F (20 °C))	
Hold-In Power Consumption In W	1.8 W 68 °F (20 °C)	
Heat Dissipation	1.8 W	
Control Circuit Voltage Limits	Operational: 0.71.3 Uc (at <122 °F (50 °C))	
	Drop-out: >= 0.10 Uc (at <122 °F (50 °C))	
Connections - Terminals	screw clamp terminals 1 0.000.01 in² (1.54 mm²)solid	
	screw clamp terminals 1 0.000.01 in² (0.754 mm²)flexible without cable end	
	screw clamp terminals 1 0.000.00 in² (0.342.5 mm²)flexible with cable end	
	screw clamp terminals 2 0.000.01 in² (1.54 mm²)solid	
	screw clamp terminals 2 0.000.01 in² (0.754 mm²)flexible without cable end screw clamp terminals 2 0.000.00 in² (0.341.5 mm²)flexible with cable end	
	Power circuit screw clamp terminals 2 0.00 in (0.041.5 mm²)flexible with cable end	
Maximum Operating Rate	3600 cyc/h	
Coil Technology	Built-in bidirectional peak limiting diode suppressor	
Mounting Support	Rail	
	Plate	
Tightening Torque	7.0811.51 lbf.in (0.81.3 N.m) screw clamp terminals Philips No 2	
	7.0811.51 lbf.in (0.81.3 N.m) screw clamp terminals flat Ø 6 mm	
	7.0811.51 lbf.in (0.81.3 N.m) screw clamp terminals pozidriv No 2	
Operating Time	1020 ms coil de-energisation and NO opening	
	3040 ms coil energisation and NO closing	
	2535 ms coil energisation and NC opening 1525 ms coil de-energisation and NC closing	
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1	
odicty Reliability Level	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1	
Mechanical Durability	30 Mcycles	
Electrical Durability	0.16 Mcycles 20 A AC-1 <= 690 V	
Height	2.28 in (58 mm)	
Width	1.77 in (45 mm)	
Depth	2.24 in (57 mm)	
Net Weight	0.52 lb(US) (0.235 kg)	
Facilities and the second of t		
Environment		
Standards	EN/IEC 60947-4-1	

Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4
Product Certifications	CB Scheme CCC UL CSA EAC CE
Ip Degree Of Protection	IP2X
Ambient Air Temperature For Operation	-13122 °F (-2550 °C)
Ambient Air Temperature For Storage	-58176 °F (-5080 °C)
Operating Altitude	6561.68 ft (2000 m) without derating

Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

## Ordering and shipping details

Category	US10I1222321	
Discount Schedule	0112	
Gtin	3389110498912	
Returnability	Yes	
Country Of Origin	FR	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.89 in (4.8 cm)
Package 1 Width	2.36 in (6.0 cm)
Package 1 Length	2.56 in (6.5 cm)
Package 1 Weight	7.80 oz (221.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	40
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	20.76 lb(US) (9.415 kg)

#### **Contractual warranty**

Warranty 18 months

## Sustainability Green Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov