

# Product data sheet

Specifications



## TeSys Deca thermal overload relays - 0.63...1 A - class 20

LR3D05L6

Discontinued on: Oct 8, 2021

Discontinued

### Main

Range	TeSys
Product Name	TeSys LRD TeSys Deca
Product Or Component Type	Non differential thermal overload relay
Device Short Name	LR3D
Relay Application	Motor protection
Product Compatibility	LC1D12 LC1D32 LC1D25 LC1D38 LC1D18 LC1D09
Network Type	DC AC
Thermal Overload Class	Class 20 IEC 60947-4-1
Thermal Protection Adjustment Range	0.63...1 A
[Ui] Rated Insulation Voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 690 V IEC 60947-4-1

### Complementary

Network Frequency	0...400 Hz
Mounting Support	Plate, with specific accessories Rail, with specific accessories Under contactor
Tripping Threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A signalling circuit
Permissible Current	3 A 120 V AC-15 signalling circuit 0.22 A 125 V DC-13 signalling circuit
[Ue] Rated Operational Voltage	690 V AC 0...400 Hz power circuit IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit 4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control Type	Red push-button stop Blue push-button reset

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Temperature Compensation	-4...140 °F (-20...60 °C)
Connections - Terminals	Control circuit screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) flexible without cable end Control circuit screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) solid without cable end Power circuit lugs-ring terminals
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 20.36 lbf.in (2.3 N.m) lugs-ring terminals M4
Height	2.60 in (66 mm)
Width	1.77 in (45 mm)
Depth	2.99 in (76 mm)
Net Weight	0.32 lb(US) (0.144 kg)

## Environment

Climatic Withstand	IACS E10
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-4...140 °F (-20...60 °C) without derating IEC 60947-4-1
Ambient Air Temperature For Storage	-76...158 °F (-60...70 °C)
Mechanical Robustness	Shocks15 Gn for 11 ms IEC 60068-2-7 Vibrations3 GN IEC 60068-2-6
Dielectric Strength	1.89 kV 50 Hz IEC 60947-1
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 EN 50495
Product Certifications	IEC UL CSA EAC ABS ATEX INERIS

## Ordering and shipping details

Category	22347-CONTACTOR,D-LINE,OVERLOADS-NEW
Discount Schedule	I12
Gtin	3606480609893
Returnability	No
Country Of Origin	TH

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.27 in (8.3 cm)
Package 1 Width	2.83 in (7.2 cm)
Package 1 Length	1.77 in (4.5 cm)
Package 1 Weight	5.08 oz (144 g)

# Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

Certifications & Standards

Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: Cancer - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>