Product data sheet

Specification





TeSys Deca, thermal overload relay, 55 to 70 A, class 10A, for LC1D80 and LC1D95

LRD3361

Product availability: Stock - Normally stocked in distribution facility

Price*: 127.00 USD

Main

Range	TeSys
Product Name	TeSys LRD TeSys Deca
Product Or Component Type	Differential thermal overload relay
Device Short Name	LRD
Relay Application	Motor protection
Product Compatibility	LC1D95 LC1D80
Network Type	DC AC
Thermal Overload Class	Class 10A IEC 60947-4-1
Thermal Protection Adjustment Range	5570 A
[Ui] Rated Insulation Voltage	Power circuit 1000 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL

Complementary

Network Frequency	0400 Hz
Mounting Support	Plate, with specific accessories Rail, with specific accessories Under contactor
Tripping Threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A signalling circuit
Permissible Current	0.72 A 500 V AC-15 signalling circuit 0.06 A 440 V DC-13 signalling circuit
[Ue] Rated Operational Voltage	1000 V AC 0400 Hz power circuit IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit 4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control Type	Red push-button stop Blue push-button reset
Temperature Compensation	-4140 °F (-2060 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Connections - Terminals	Power circuit corew clamp terminals 1 0.01 0.05 in ² (4 . 35 mm ²) flexible without		
Connections - Terminals	Power circuit screw clamp terminals 1 0.010.05 in² (435 mm²) flexible without cable end Power circuit screw clamp terminals 1 0.010.05 in² (435 mm²) flexible with cable end Power circuit screw clamp terminals 1 0.010.05 in² (435 mm²) solid without cable end		
			Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) flexible without cable end
		Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) solid without cable end	
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals		
	Power circuit 79.66 lbf.in (9 N.m) screw clamp terminals		
Height	3.19 in (81 mm)		
Width	2.76 in (70 mm)		
Depth	4.53 in (115 mm)		
Net Weight	1.12 lb(US) (0.51 kg)		

Environment

Climatic Withstand	IACS E10	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ambient Air Temperature For Operation	-4140 °F (-2060 °C) without derating IEC 60947-4-1	
Ambient Air Temperature For Storage	-76158 °F (-6070 °C)	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations6 Gn IEC 60068-2-6 Shocks15 Gn for 11 ms IEC 60068-2-7	
Dielectric Strength 2.2 kV 50 Hz IEC 60947-1		
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495	
Product Certifications	IEC UL CSA CCC EAC ATEX INERIS UKCA	

Ordering and shipping details

Category	US10I1222347
Discount Schedule	0112
Gtin	3389110519983
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE

1
3.15 in (8.000 cm)
4.69 in (11.900 cm)
3.39 in (8.600 cm)
17.99 oz (510.000 g)
S02
12
5.91 in (15.000 cm)
11.81 in (30.000 cm)
15.75 in (40.000 cm)
14.22 lb(US) (6.450 kg)
P06
192
29.53 in (75.000 cm)
23.62 in (60.000 cm)
31.50 in (80.000 cm)
250.67 lb(US) (113.700 kg)

Contractual warranty

Warranty 18 months

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov