# **Product data sheet**

Specification





# Non differential thermal overload relays, TeSys K, 0.54 to 0.8 A, class 10A

LR7K0305

! Discontinued

#### Main

Range	TeSys	
Product Name	TeSys LRK	
Product Or Component Type	Non differential thermal overload relay	
Device Short Name	LR7K	
Relay Application	Motor protection	
Product Compatibility	LC7K LP1K LC1K LP4K	
Network Type	DC AC	
Thermal Overload Class	Class 10A IEC 60947-4-1	
Thermal Protection Adjustment Range	0.540.8 A	
[Ui] Rated Insulation Voltage	Power circuit 690 V BS 4941 Power circuit 690 V IEC 60947 Power circuit 750 V VDE 0110 group C Power circuit 600 V CSA C22.2 No 14	

#### Complementary

Network Frequency	<= 400 Hz
	17 TOU TIZ
Mounting Support	Under contactor
	Plate, with specific accessories
	Rail, with specific accessories
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	6 A signalling circuit
[Ue] Rated Operational Voltage	<= 690 V power circuit
	690 V AC AC-15 signalling circuit
	250 V DC DC-13 signalling circuit
Associated Fuse Rating	6 A gG for signalling circuit conforming to VDE 0660
	6 A gG for signalling circuit conforming to IEC 60947
[Uimp] Rated Impulse Withstand Voltage	6 kV
Power Dissipation Per Pole	2 W
Local Signalling	Trip indicator Yellow)
Control Type	Red push-button trip test function
<b>.</b>	· · · · · · · · · · · · · · · · · · ·
	selector switch manual or automatic reset
	Red push-button trip test function Blue push-button stop and manual reset

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Connections - Terminals	screw clamp terminals 1 0.000.01 in² (1.54 mm²)solid screw clamp terminals 2 0.000.01 in² (1.54 mm²)solid	
	screw clamp terminals 1 0.000.01 in² (0.754 mm²)flexible without cable end screw clamp terminals 2 0.000.01 in² (0.754 mm²)flexible without cable end screw clamp terminals 1 0.000.00 in² (0.342.5 mm²)flexible with cable end screw clamp terminals 2 0.000.00 in² (0.341.5 mm²)flexible with cable end	
Tightening Torque	11.51 lbf.in (1.3 N.m) screw clamp terminals Philips No 2 11.51 lbf.in (1.3 N.m) screw clamp terminals flat Ø 6 mm 11.51 lbf.in (1.3 N.m) screw clamp terminals pozidriv No 2	
Height	2.28 in (58 mm)	
Width	1.77 in (45 mm)	
Depth	2.56 in (65 mm)	
Net Weight	0.32 lb(US) (0.145 kg)	

#### **Environment**

Standards	BS 4941 IEC 60947	
	NF C 63-650 VDE 0660	
Product Certifications	UL CSA	
	UKCA	
Protective Treatment	TC IEC 60068 TC DIN 50016	
Ip Degree Of Protection	IP2X conforming to IEC 60529	
Ambient Air Temperature For Operation	-4131 °F (-2055 °C) without derating IEC 60947 -22140 °F (-3060 °C) with derating IEC 60947	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Operating Altitude	6561.68 ft (2000 m) without derating	
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102	
Mechanical Robustness	Shocks NO contact10 Gn for 11 ms IEC 60068-2-27 Shocks NC contact10 Gn for 11 ms IEC 60068-2-27 Vibrations NO contact2 Gn, 5300 Hz IEC 60068-2-6 Vibrations NC contact2 Gn, 5300 Hz IEC 60068-2-6	

## Ordering and shipping details

Category	22314-**OBS**CTR,D-LINE,OVERLOADS
Discount Schedule	112
Gtin	3389110705904
Returnability	No
Country Of Origin	C7

## **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.89 in (4.8 cm)	
Package 1 Width	2.83 in (7.2 cm)	
Package 1 Length	3.35 in (8.5 cm)	

Package 1 Weight	5.22 oz (148.0 g)	
Unit Type Of Package 2	S02	
Number Of Units In Package 2	41	
Package 2 Height	5.91 in (15.0 cm)	
Package 2 Width	11.81 in (30.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	14.51 lb(US) (6.58 kg)	

### **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov