# **Product data sheet**

Specification





# Thermal overload relay,TeSys Deca,0.25-0.4A,1NO+1NC,class 10A,lug terminal

LRD036

! Discontinued

#### Main

Range	TeSys
Product Name	TeSys LRD
	TeSys Deca
Product Or Component Type	Differential thermal overload relay
Device Short Name	LRD
Relay Application	Motor protection
Product Compatibility	LC1D18
	LC1D09
	LC1D12
	LC1D25
	LC1D32
	LC1D38
Network Type	DC
	AC
Thermal Overload Class	Class 10A IEC 60947-4-1
Thermal Protection Adjustment Range	0.250.4 A
[Ui] Rated Insulation Voltage	Power circuit 600 V CSA
	Power circuit 600 V UL
	Power circuit 690 V IEC 60947-4-1

#### Complementary

Network Frequency	0400 Hz
Mounting Support	Plate, with specific accessories
	Rail, with specific accessories
	Under contactor
Tripping Threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A signalling circuit
Permissible Current	3 A 120 V AC-15 signalling circuit
	0.22 A 125 V DC-13 signalling circuit
[Ue] Rated Operational Voltage	690 V AC 0400 Hz power circuit IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit
v	4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control Type	Red push-button stop
	Blue push-button reset

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Temperature Compensation	-4140 °F (-2060 °C)
Connection Pitch	0.57 in (14.5 mm)
Connections - Terminals	Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) flexible without cable end Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) flexible with cable end Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) solid without cable end Power circuit lugs-ring terminals
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 20.36 lbf.in (2.3 N.m) lugs-ring terminals M4
Height	2.60 in (66 mm)
Width	1.77 in (45 mm)
Depth	2.76 in (70 mm)
Net Weight	0.27 lb(US) (0.124 kg)

#### **Environment**

Climatic Withstand	IACS E10
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-4140 °F (-2060 °C) without derating IEC 60947-4-1
Ambient Air Temperature For Storage	-76158 °F (-6070 °C)
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations6 Gn IEC 60068-2-6 Shocks15 Gn for 11 ms IEC 60068-2-7
Dielectric Strength	1.89 kV 50 Hz IEC 60947-1
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495
Product Certifications	IEC UL CSA CCC EAC BV RINA DNV-GL LROS (Lloyds register of shipping) ATEX INERIS UKCA

## Ordering and shipping details

Category	22347-CONTACTOR,D-LINE,OVERLOADS-NEW
Discount Schedule	112
Gtin	3389110822472
Returnability	No
Country Of Origin	FR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.54 in (9.0 cm)
Package 1 Width	3.03 in (7.7 cm)
Package 1 Length	1.93 in (4.9 cm)
Package 1 Weight	5.15 oz (146.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	24
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	8.73 lb(US) (3.959 kg)

## **Contractual warranty**

Warranty 18 months

### Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov