

Product data sheet

Specifications



EcoStruxure Building Expert EnOcean DIN rail mounted room controller

LSS10020025

⚠ Discontinued on: Dec 1, 2020

⚠ Discontinued

Main

Range	EcoStruxure Building Expert
Product Name	EnOcean
Product Or Component Type	Room controller
Communication Interface	Radio
Device Application	Switching loads

Complementary

Mounting Support	DIN rail
Transmission Frequency	868.3 MHz
[Us] Rated Supply Voltage	230 V 50 Hz
Load Type	Resistive 1100 VA 1 Incandescent 400 W Inductive 360 W 0.4...0.6
Ip Degree Of Protection	IP20

Environment

Ambient Air Temperature For Operation	14...131 °F (-10...55 °C)
Ambient Air Temperature For Storage	-40...176 °F (-40...80 °C)
Marking	CE

Ordering and shipping details

Gtin	7332552010644
------	---------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	3.54 in (9 cm)
Package 1 Length	0.71 in (1.8 cm)
Package 1 Weight	2.33 oz (66 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--
