

Product data sheet

Specifications

EBE - EnOcean 868MHz - Outdoor temperature sensor



LSS10020046

⚠ Discontinued on: Oct 28, 2022

⚠ Discontinued

Main

| | |
|----------------------------|-----------------------------|
| Range | EcoStruxure Building Expert |
| Product Name | EnOcean |
| Product Or Component Type | Temperature sensor |
| Function Available | With temperature sensor |
| Communication Network Type | Wireless |

Complementary

| | |
|------------------------|---------------|
| Type Of Measurement | Temperature - |
| Type Of Installation | Outdoor |
| Transmission Frequency | 868 kHz |
| Transmitting Range | 30 m |

Ordering and shipping details

| | |
|------|---------------|
| Gtin | 7332552010583 |
|------|---------------|

Packing Units

| | |
|------------------------------|------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 0.59 in (1.5 cm) |
| Package 1 Width | 3.07 in (7.8 cm) |
| Package 1 Length | 1.02 in (2.6 cm) |
| Package 1 Weight | 1.41 oz (40 g) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)
