Product data sheet

Specification





Standard control unit, TeSys Ultra, 8A to 32A, 3P motors, thermal magnetic protection, class 10, coil 48-72VAC/DC

LUCA32ES

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 120.00 USD

Main

Range	TeSys
Range Of Product	TeSys Ultra
Product Name	TeSys Ultra
Device Short Name	LUCA
Product Or Component Type	Standard control unit
Device Application	Motor control Motor protection
Product Specific Application	Basic protection requirements for motor starters: overload and short-circuit
Main Function Available	Earth fault protection Protection against phase failure and phase imbalance Manual reset Protection against overload and short-circuit
Product Compatibility	Power base LUB32 Power base LUB38 Power base LUB320 Power base LUB380 Reversing contactor breaker LU2B32ES
[Ue] Rated Operational Voltage	690 V AC
Network Frequency	4060 Hz
Load Type	3-phase motor self-cooled
Utilisation Category	AC-41 AC-43 AC-44
Motor Power Kw	15 kW 400440 V AC 50/60 Hz 15 kW 500 V AC 50/60 Hz 18.5 kW 690 V AC 50/60 Hz
Rated Motor Current Adjustment Range	832 A
Thermal Overload Class	Class 10 4060 Hz -13158 °F (-2570 °C) IEC 60947-6-2 Class 10 4060 Hz -13158 °F (-2570 °C) UL 508
Tripping Threshold	14.2 x lr +/- 20 %
Phase Failure Sensitivity	Yes
[Uc] Control Circuit Voltage	48 V AC 4872 V DC

Complementary

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Control Circuit Voltage Limits	38.572 V AC 48 V in operation
	38.593 V DC 4872 V in operation
	29 V AC 48 V drop-out
	29 V DC 4872 V drop-out
Typical Current Consumption	280 mA 48 V AC I maximum while closing with LUB32
	280 mA 48 V AC I maximum while closing with LUB38
	280 mA 4872 V DC I maximum while closing with LUB32
	280 mA 4872 V DC I maximum while closing with LUB38
	45 mA 48 V AC I rms sealed with LUB32
	45 mA 48 V AC I rms sealed with LUB38
	45 mA 4872 V DC I rms sealed with LUB32 45 mA 4872 V DC I rms sealed with LUB38
Heat Dissipation	3 W control circuit with LUB32
	3 W control circuit with LUB38
Operating Time	35 ms opening with LUB32 control circuit
	35 ms opening with LUB38 control circuit
	60 ms closing with LUB32 control circuit
	60 ms closing with LUB38 control circuit
Standards	EN 60947-6-2
	IEC 60947-6-2
	UL 60947-4-1, with phase barrier
	CSA C22.2 No 60947-4-1, with phase barrier
Product Certifications	CE
	UL
	CSA
	CCC
	EAC ASEFA
	ATEX
	Marine
[Hi] Batad Inculation Voltage	0001/150 00047.0.0
[Ui] Rated Insulation Voltage	690 V IEC 60947-6-2 600 V UL 60947-4-1
	600 V CSA C22.2 No 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-6-2
Safe Separation Of Circuit	400 V SELV between the control and auxiliary circuits IEC 60947-1
	400 V SELV between the control or auxiliary circuit and the main circuit IEC 60947-1
Fixing Mode	Plug-in (front face)
Width	1.77 in (45 mm)
Height	2.60 in (66 mm)
Depth	2.36 in (60 mm)
Net Weight	0.30 lb(US) (0.135 kg)
Compatibility Code	LUCA
Environment	
Ip Degree Of Protection	IP20 front panel and wired terminals IEC 60947-1
	IP20 other faces IEC 60947-1 IP40 front panel outside connection zone IEC 60947-1
Protective Treatment	TH IEC 60068
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Operating Altitude	6561.68 ft (2000 m)
Fire Resistance	1760 °F (960 °C) parts supporting live components IEC 60695-2-12
Fire Resistance	1760 °F (960 °C) parts supporting live components IEC 60695-2-12 1202 °F (650 °C) IEC 60695-2-12
Fire Resistance Shock Resistance	

Vibration Resistance	2 gn 5300 Hz power poles open IEC 60068-2-6 4 gn 5300 Hz power poles closed IEC 60068-2-6
Resistance To Electrostatic Discharge	8 kV 3 in open air IEC 61000-4-2 8 kV 4 on contact IEC 61000-4-2
Non-Dissipating Shock Wave	1 kV serial mode IEC 60947-6-2 2 kV common mode IEC 60947-6-2
Resistance To Radiated Fields	9.14 V/m (10 V/m) 3 IEC 61000-4-3
Resistance To Fast Transients	2 kV 3 serial link IEC 61000-4-4 4 kV 4 all circuits except for serial link IEC 61000-4-4
Immunity To Radioelectric Fields	10 V IEC 61000-4-6
Immunity To Microbreaks	3 ms
Immunity To Voltage Dips	70 % / 500 ms IEC 61000-4-11

Ordering and shipping details

Category	US10I1122397
Discount Schedule	0111
Gtin	3389110363999
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	3.15 in (8.000 cm)
Package 1 Length	3.35 in (8.500 cm)
Package 1 Weight	4.44 oz (126.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	23
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	7.04 lb(US) (3.194 kg)

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information