# Product data sheet

Specifications





Advanced control unit, TeSys Ultra, 1.25A to 5A, 3P motors, protection & diagnostic, class 10, coil 24VAC

LUCB05B

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 150.00 USD

### Main

Range	TeSys
Range Of Product	TeSys Ultra
Product Name	TeSys Ultra
Device Short Name	LUCB
Product Or Component Type	Advanced control unit
Device Application	Motor control
	Motor protection
Product Specific Application	Basic protection and advanced functions, communication
Main Function Available	Earth fault protection
	Protection against phase failure and phase imbalance
	Manual reset
	Protection against overload and short-circuit
Product Compatibility	Power base LUB12
	Power base LUB32
	Power base LUB38
	Power base LUB120
	Power base LUB320
	Power base LUB380
	Reversing contactor breaker LU2B12B
	Reversing contactor breaker LU2B32B
[Ue] Rated Operational Voltage	690 V AC
Network Frequency	4060 Hz
Load Type	3-phase motor self-cooled
Utilisation Category	AC-43
	AC-44
	AC-41
Motor Power Kw	1.5 kW 400440 V AC 50/60 Hz
	2.2 kW 500 V AC 50/60 Hz
	3 kW 690 V AC 50/60 Hz
Rated Motor Current Adjustment Range	1.255 A
Thermal Overload Class	Class 10 4060 Hz -13158 °F (-2570 °C) IEC 60947-6-2 Class 10 4060 Hz -13158 °F (-2570 °C) UL 508
Tripping Throshold	· · · · · ·
Tripping Threshold	14.2 x lr +/- 20 %
Phase Failure Sensitivity	Yes
[Uc] Control Circuit Voltage	24 V AC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

### Complementary

Complementary	
Control Circuit Voltage Limits	2026.5 V AC 24 V in operation 14.5 V AC 24 V drop-out
Typical Current Consumption	140 mA 24 V AC I maximum while closing with LUB12 220 mA 24 V AC I maximum while closing with LUB32 220 mA 24 V AC I maximum while closing with LUB38 70 mA 24 V AC I rms sealed with LUB12 90 mA 24 V AC I rms sealed with LUB32 90 mA 24 V AC I rms sealed with LUB38
Heat Dissipation	2 W control circuit with LUB12 3 W control circuit with LUB32 3 W control circuit with LUB38
Operating Time	35 ms opening with LUB32 control circuit 35 ms opening with LUB32 control circuit 35 ms opening with LUB38 control circuit 70 ms closing with LUB12 control circuit 70 ms closing with LUB32 control circuit 70 ms closing with LUB38 control circuit
Reset	Manual reset
Standards	EN 60947-6-2 IEC 60947-6-2 UL 60947-4-1, with phase barrier CSA C22.2 No 60947-4-1, with phase barrier
Product Certifications	CE UL CSA CCC EAC ASEFA ATEX Marine
[Ui] Rated Insulation Voltage	690 V IEC 60947-6-2 600 V UL 60947-4-1 600 V CSA C22.2 No 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-6-2
Safe Separation Of Circuit	400 V SELV between the control and auxiliary circuits IEC 60947-1 400 V SELV between the control or auxiliary circuit and the main circuit IEC 60947-1
Fixing Mode	Plug-in (front face)
Width	1.77 in (45 mm)
Height	2.60 in (66 mm)
Depth	2.36 in (60 mm)
Compatibility Code	LUCB

### **Environment**

Ip Degree Of Protection	IP20 front panel and wired terminals IEC 60947-1 IP20 other faces IEC 60947-1 IP40 front panel outside connection zone IEC 60947-1
Protective Treatment	TH IEC 60068
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Operating Altitude	6561.68 ft (2000 m)
Fire Resistance	1760 °F (960 °C) parts supporting live components IEC 60695-2-12 1202 °F (650 °C) IEC 60695-2-12
Shock Resistance	10 gn power poles open IEC 60068-2-27 15 gn power poles closed IEC 60068-2-27

Vibration Resistance	2 gn 5300 Hz power poles open IEC 60068-2-6 4 gn 5300 Hz power poles closed IEC 60068-2-6
Resistance To Electrostatic Discharge	8 kV 3 in open air IEC 61000-4-2 8 kV 4 on contact IEC 61000-4-2
Non-Dissipating Shock Wave	1 kV serial mode IEC 60947-6-2 2 kV common mode IEC 60947-6-2
Resistance To Radiated Fields	9.14 V/m (10 V/m) 3 IEC 61000-4-3
Resistance To Fast Transients	2 kV 3 serial link IEC 61000-4-4 4 kV 4 all circuits except for serial link IEC 61000-4-4
Immunity To Radioelectric Fields	10 V IEC 61000-4-6
Immunity To Microbreaks	3 ms
Immunity To Voltage Dips	70 % / 500 ms IEC 61000-4-11

# Ordering and shipping details

Category	US10I1122397
Discount Schedule	0111
Gtin	3389110364149
Returnability	No
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	3.23 in (8.200 cm)
Package 1 Length	3.39 in (8.600 cm)
Package 1 Weight	3.99 oz (113.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	23
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	6.39 lb(US) (2.900 kg)

## **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium\*

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>⊘</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information