Product data sheet

Specification





Circuit breaker frame, MasterPact MTZ2 16H2 fixed for MicroLogic X, 1600A, 100kA/415VAC (Icu), 4P

LV848051

Main

| Range | MasterPacT |
|--------------------------------|---|
| Product Name | MasterPact MTZ2 |
| Device Short Name | MTZ2 16 H2 |
| Product Or Component Type | Circuit breaker |
| Device Application | Power distribution protection |
| Poles Description | 4P |
| Neutral Position | Left |
| Control Unit | Without control unit |
| Product Compatibility | control unit MicroLogic 2.0 X control unit MicroLogic 5.0 X control unit MicroLogic 6.0 X control unit MicroLogic 7.0 X control unit MicroLogic 2.0 Xi control unit MicroLogic 5.0 Xi control unit MicroLogic 6.0 Xi control unit MicroLogic 7.0 Xi |
| Line Rated Current | 1600 A 104 °F (40 °C) |
| Performance Type | H2 100 kA 415 V AC |
| [Ue] Rated Operational Voltage | 690 V AC 50/60 Hz |
| Suitability For Isolation | Yes EN/IEC 60947-2 |
| Selectivity Category | Category B |
| Control Type | Push-button |
| Mounting Mode | Fixed |

Complementary

| [Icu] Rated Ultimate Short-Circuit Breaking Capacity | 100 kA 220/415 V AC 50/60 Hz 100 kA 440 V AC 50/60 Hz 85 kA 500/525 V AC 50/60 Hz 85 kA 660/690 V AC 50/60 Hz |
|---|--|
| [Ics] Rated Service Breaking Capacity | 100 kA 220/415 V AC 50/60 Hz 100 kA 440 V AC 50/60 Hz 85 kA 500/525 V AC 50/60 Hz 85 kA 660/690 V AC 50/60 Hz |
| [Icw] Rated Short-Time Withstand Current | 85 kA 0.5 s 85 kA 1 s 50 kA 3 s |
| [Icm] Rated Short-Circuit Making Capacity | 220 kA 220/415 V AC 50/60 Hz 220 kA 440 V AC 50/60 Hz 187 kA 500/525 V AC 50/60 Hz |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

187 kA 660/690 V AC 50/60 Hz

| Integrated Instantaneous Protection (Din In Ka Peak) | 171209 kA |
|---|---|
| Sensor Rating | 800 A |
| | 1000 A |
| | 1250 A |
| | 1600 A |
| [Ui] Rated Insulation Voltage | 1000 V AC 50/60 Hz |
| [Uimp] Rated Impulse Withstand Voltage | 12 kV |
| Power Dissipation In W | 170 W |
| Maximum Breaking Time | 25 ms |
| Maximum Closing Response Time | 70 ms |
| Mounting Support | Rails |
| | Base plate |
| Upside Connection | Front |
| | Rear |
| Downside Connection | Front |
| | Rear |
| Connection Pitch | 4.53 in (115 mm) |
| Mechanical Durability | 25000 cycles with periodic preventive maintenance |
| Electrical Durability | 10000 cycles 440 V AC 50/60 Hz EN/IEC 60947-2 |
| | 10000 cycles 690 V AC 50/60 Hz EN/IEC 60947-2 |
| | AC-23A 10000 cycles 440 V AC 50/60 Hz EN/IEC 60947-3 |
| | AC-23A 10000 cycles 690 V AC 50/60 Hz EN/IEC 60947-3 |
| | AC-3 6000 cycles 440/690 V AC 50/60 Hz EN/IEC 60947-3 |
| Height | 13.86 in (352 mm) |
| Width | 21.14 in (537 mm) |
| Depth | 11.81 in (300 mm) |
| Net Weight | 143.30 lb(US) (65 kg) |
| Standards | EN/IEC 60947-1 |
| | EN/IEC 60947-2 |
| | EN/IEC 60947-2 Annex H |
| | IEC 61557-12 |
| Product Certifications | CE |
| | IECEE CB Scheme |
| | |

Environment

| Ip Degree Of Protection | IP30 conforming to EN 60529 |
|---------------------------------------|---|
| Pollution Degree | 3 IEC 60947-1 |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |
| Ambient Air Temperature For Storage | -40185 °F (-4085 °C) |
| Operating Altitude | 06561.68 ft (02000 m) without derating 20005000 m with derating |

Ordering and shipping details

Gtin 3606480808357

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1 |

| Package 1 Height | 11.61 in (29.5 cm) |
|------------------|---------------------------|
| Package 1 Width | 12.01 in (30.5 cm) |
| Package 1 Length | 19.49 in (49.5 cm) |
| Package 1 Weight | 104.17 lb(US) (47.251 kg) |

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| | Mercury Free | |
|----------|----------------------------|-----|
| | Rohs Exemption Information | Yes |
| Ø | Pvc Free | |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |