Product data sheet

Specifications





TeSys Deca thermal overload relays - 30...40 A - class 20

LRD340L

Product availability: Stock - Normally stocked in distribution facility

Price*: 107.00 USD

Main

Range	TeSys TeSys Deca	
Product Name	TeSys LRD TeSys Deca	
Product Or Component Type	Differential thermal overload relay	
Device Short Name	LRD	
Relay Application	Motor protection	
Product Compatibility	LC1D50A LC1D65A LC1D40A	
Network Type	AC DC	
Thermal Overload Class	Class 20 IEC 60947-4-1	
Thermal Protection Adjustment Range		
[Ui] Rated Insulation Voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 690 V IEC 60947-4-1	

Complementary

Network Frequency	0400 Hz
Mounting Support	Plate, with specific accessories Rail, with specific accessories Under contactor
Tripping Threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A signalling circuit
Permissible Current	3 A 120 V AC-15 signalling circuit 0.22 A 125 V DC-13 signalling circuit
[Ue] Rated Operational Voltage	690 V AC 0400 Hz power circuit IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit 4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control Type	Red push-button stop Blue push-button reset
Temperature Compensation	-4140 °F (-2060 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Connections - Terminals	Control circuit screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) flexible with cable end Control circuit screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) solid without cable end Power circuit EverLink BTR screw connectors 1 0.000.05 in ² (135 mm ²) flexible without cable end Power circuit EverLink BTR screw connectors 1 0.000.05 in ² (135 mm ²) flexible with cable end Power circuit EverLink BTR screw connectors 1 0.000.05 in ² (135 mm ²) flexible with cable end Power circuit EverLink BTR screw connectors 1 0.000.05 in ² (135 mm ²) flexible with cable end
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 44.25 lbf.in (5 N.m) EverLink BTR screw connectors
Height	2.76 in (70 mm)
Width	2.17 in (55 mm)
Depth	4.84 in (123 mm)
Net Weight	0.83 lb(US) (0.375 kg)

Environment

Climatic Withstand	IACS E10	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ambient Air Temperature For Operation	-4140 °F (-2060 °C) without derating IEC 60947-4-1	
Ambient Air Temperature For Storage	-76158 °F (-6070 °C)	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Shocks15 Gn for 11 ms IEC 60068-2-7 Vibrations4 gn IEC 60068-2-6	
Dielectric Strength	1.89 kV 50 Hz IEC 60947-1	
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5	
Product Certifications	IEC UL CSA CCC EAC DNV-GL RMRS EU-RO MR LROS (Lloyds register of shipping) UKCA	

Ordering and shipping details

Category	US10I1222347	
Discount Schedule	0112	
Gtin	3389119215565	
Returnability	Yes	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	4.33 in (11 cm)
Package 1 Length	5.51 in (14 cm)
Package 1 Weight	14.46 oz (410 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	13
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	12.43 lb(US) (5.637 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

9	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov