Product data sheet

Specifications



Circuit breaker, PowerPacT L, 400A, 4 pole, 600VAC, 100kA, lugs, MicroLogic 6.3E, 80%

LRL46400U54X

Main

_		
Range	PowerPact	
Product Name	PowerPact L	
Device Short Name	L-Frame	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

Complementary

Complementary	
Line Rated Current	400 A
Number Of Poles	4P
Control Type	Toggle
Breaking Capacity Code	R
Breaking Capacity	200 kA 240 V AC 50/60 Hz UL 489 200 kA 480 V AC 50/60 Hz UL 489 100 kA 600 V AC 50/60 Hz UL 489
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz IEC 60947-3
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	150 kA 220/240 V AC 50/60 Hz IEC 60947-2 125 kA 380/440/415 V AC 50/60 Hz IEC 60947-2 75 kA 500/525 V AC 50/60 Hz IEC 60947-2 20 kA 690 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Electronic, energy, MicroLogic 6.3 E, LSIG
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	750 V IEC 60947-2
Trip Unit Name	MicroLogic 6.3 E
Protection Technology	Current limiter
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A
Awg Gauge	AWG 2/0500 kcmil aluminium/copper
Local Signalling	Ready 1 LED green) Alarm 1 LED 90 % Ir orange) Alarm LED 105 % Ir red) Switched off (OFF) 1 trip indicator green)
Mounting Mode	Unit mount lug)
Mounting Support	Lug

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Electrical Connection	Lugs, line Lugs, load
Terminal Identifier	AL600LS52K4
Long Time Pick-Up Adjustment Range	0.251 x ln
Tightening Torque	442.54 lbf.in (50 N.m) 0.110.37 in² (70240 mm²) (AWG 2/0500 kcmil)
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)
Power Wire Stripping Length	1.22 in (31 mm)
Color	Black
Height	13.39 in (340 mm)
Width	5.51 in (140 mm)
Depth	4.33 in (110 mm)
Net Weight	13.67 lb(US) (6.2 kg)
Communication Interface	Modbus Ethernet

Environment

Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2	
Product Certifications	UL CSA NOM	
Ip Degree Of Protection	Front cover IP40	
Pollution Degree	3 IEC 60947-1	
Ambient Air Temperature For Operation	28158 °F (-270 °C)	
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)	
Operating Altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating	

Ordering and shipping details

Category	01119-L HIGH INTERUPT UNIT MT BREAKER/SW	
Discount Schedule	DE2	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.94 in (35.4 cm)
Package 1 Width	7.28 in (18.5 cm)
Package 1 Length	6.61 in (16.8 cm)
Package 1 Weight	14.00 lb(US) (6.35 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov