

Product data sheet

Specifications



Motor Management, TeSys T, motor controller, CANopen, 6 logic inputs, 3 relay logic outputs, 0.4 to 8A, 24 VDC

LTMR08CBD

⚠ To be discontinued

⚠ To be discontinued on: Jul 31, 2025

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 750.00 USD

Main

Range	TeSys
Product Name	TeSys T
Device Short Name	LTMR
Product Or Component Type	Motor controller
Device Application	Equipment monitoring and control
Measurement Current	0.4...8 A
[Us] Rated Supply Voltage	24 V DC
Current Consumption	56...127 mA
Supply Voltage Limits	20.4...26.24 V DC
Communication Port Protocol	CANopen
Bus Type	CANopen ISO 1198 1...127 10...1000 kbit/s, SUB-D 9 4 twisted shielded pairs cable CANopen ISO 1198 1...127 10...1000 kbit/s, terminal block 4 twisted shielded pairs cable

Complementary

[Ui] Rated Insulation Voltage	690 V EN/IEC 60947-1 690 V CSA C22.2 No 14 690 V UL 508
[Uimp] Rated Impulse Withstand Voltage	6 kV current or voltage measurement circuit EN/IEC 60947-4-1 0.8 kV communication circuit EN/IEC 60947-4-1 0.8 kV supply, inputs and outputs EN/IEC 60947-4-1
Short-Circuit Withstand	100 kA conforming to EN/IEC 60947-4-1
Associated Fuse Rating	4 A gG output 0.5 A gG control circuit
Protection Type	Overload (long time) Phase failure Load fluctuation Phase imbalance Reverse polarity protection Thermal protection Thermal overload protection Earth-leakage protection Power factor variation Overload Locked rotor

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Network And Machine Diagnosis Type	Trip context information Remaining operating time before overload tripping Starting current and time Event recording Motor control command recording Running hours counter/operating time Waiting time after overload tripping Trip history information Phase fault and earth fault trip counters Fault recording
Logic Input Number	6
Input Current	7 mA
Current State 0 Guaranteed	Logic input < 5 V <= 15 mA 5 ms
Current State 1 Guaranteed	Logic input < 15 V 2...15 mA 15 ms
Maximum Output Switching Frequency	2 Hz
Load Current	5 A 250 V AC logic output 5 A 30 V DC logic output
Permissible Power	480 VA AC-15), I _e = 2 A, 500000 cycles output) 30 W DC-13), I _e = 1.25 A, 500000 cycles output)
Maximum Operating Rate	1800 cyc/h
Contacts Type And Composition	1 NO + 1 NC fault signal 3 NO
Metering Type	Average current I _{avg} Phase current I ₁ , I ₂ , I ₃ RMS Temperature Earth-fault current Imbalance current
Measurement Accuracy	5...15 % earth fault current internal measurement 1 % voltage 100...830 V) 3 % power factor 5 % earth fault current external measurement +/- 30 min/year internal clock 0,02 Temperature 1 % current 5 % active and reactive power
Overvoltage Category	III
Connection Pitch	0.20 in (5.08 mm)
Connections - Terminals	Control circuit connector 1 0.00...0.00 in ² (0.25...2.5 mm ²) AWG 24...AWG 14)flexible with cable end Control circuit connector 1 0.00...0.00 in ² (0.2...2.5 mm ²) AWG 24...AWG 14)flexible without cable end Control circuit connector 1 0.00...0.00 in ² (0.25...2.5 mm ²) AWG 24...AWG 14)flexible without cable end Control circuit connector 1 0.00...0.00 in ² (0.2...2.5 mm ²) AWG 24...AWG 14)solid without cable end Control circuit connector 2 0.00...0.00 in ² (0.2...1 mm ²) AWG 24...AWG 14)flexible with cable end Control circuit connector 2 0.00...0.00 in ² (0.2...1.5 mm ²) AWG 24...AWG 14)flexible without cable end Control circuit connector 2 0.00...0.00 in ² (0.5...1.5 mm ²) AWG 24...AWG 14)flexible without cable end Control circuit connector 2 0.00...0.00 in ² (0.2...1 mm ²) AWG 24...AWG 14)solid without cable end
Tightening Torque	Control circuit 4.43...5.31 lbf.in (0.5...0.6 N.m) flat 0.12 in (3 mm)
Pollution Degree	3

Electromagnetic Compatibility	Electrostatic discharge, 3, 8 kV air, 6 kV contact, conforming to EN/IEC 61000-4-2 Radiated RF fields, 3, 10 V/m, conforming to EN/IEC 61000-4-3 Fast transients immunity test (other circuits), level 3, 2 kV, conforming to EN/IEC 61000-4-4 Fast transients immunity test (on supply and relay outputs), level 4, 4 kV, conforming to EN/IEC 61000-4-4 Voltage dips and interruptions immunity test, 70 %, 500 ms, conforming to EN/IEC 61000-4-11 Conducted RF disturbances, 10 V, conforming to EN/IEC 61000-4-6 Temperature sensor: surges (serial mode), 0.5 kV, conforming to EN/IEC 61000-4-5 Temperature sensor: surges (common mode), 1 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (serial mode), 1 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (common mode), 1 kV, conforming to EN/IEC 61000-4-5 Communication: surges (common mode), 2 kV, conforming to EN/IEC 61000-4-5 Relay outputs and supply: surges (serial mode), 2 kV, conforming to EN/IEC 61000-4-5 Relay outputs and supply: surges (common mode), 4 kV, conforming to EN/IEC 61000-4-5
Width	3.58 in (91 mm)
Height	2.40 in (61 mm)
Depth	4.82 in (122.5 mm)
Net Weight	1.17 lb(US) (0.53 kg)
Web Services	Web server
Compatibility Code	LTMR

Environment

Standards	EN 60947-4-1 CSA C22.2 No 14 IEC 60947-4-1 UL 508 IACS E10
Product Certifications	ATEX C-tick EAC LROS (Lloyds register of shipping) NOM BV RINA KERI ABS UL CSA DNV RMRoS GL CCC
Protective Treatment	12 x 24 hour cycles EN/IEC 60068-2-30 48 h EN/IEC 60070-2-11 TH EN/IEC 60068
Fire Resistance	1202 °F (650 °C) EN/IEC 60695-2-12 1760 °F (960 °C) UL 94
Ambient Air Temperature For Operation	-4...140 °F (-20...60 °C)
Ambient Air Temperature For Storage	-40...176 °F (-40...80 °C)
Operating Altitude	<= 6561.68 ft (2000 m) without derating
Mechanical Robustness	Vibrations mounted on symmetrical rail1 Gn, 5...300 Hz EN/IEC 60068-2-6 Vibrations plate mounted4 Gn, 5...300 Hz EN/IEC 60068-2-6 Shocks half sine wave acceleration15 Gn for 11 ms EN/IEC 60068-2-27
Ip Degree Of Protection	IP20

Ordering and shipping details

Category	US10I1222338
----------	--------------

Discount Schedule	0I12
Gtin	3389119404686
Returnability	No
Country Of Origin	KR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	3.94 in (10.0 cm)
Package 1 Length	5.31 in (13.5 cm)
Package 1 Weight	17.99 oz (510.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	10
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	12.02 lb(US) (5.452 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information