



Price\*\* : 81.90 USD



### Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D8
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	440 V AC 50/60 Hz
Average resistance	21501 Ohm at 68 °F (20 °C)
Inductance of closed circuit	507.47 H
Product compatibility	LC1D115 LC1D150
Mechanical durability	8 Mcycles
Operating rate	1200 cyc/h at <= 140 °F (60 °C)

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.5 Uc at 131 °F (55 °C) drop-out 50/60 Hz 0.8...1.15 Uc at 131 °F (55 °C) operational 50/60 Hz
Inrush power in VA	280...350 VA at 68 °F (20 °C) (cos φ 0.9) 60 Hz 280...350 VA at 68 °F (20 °C) (cos φ 0.9) 50 Hz
Hold-in power consumption in VA	2...18 VA at 68 °F (20 °C) (cos φ 0.9) 50 Hz 2...18 VA at 68 °F (20 °C) (cos φ 0.9) 60 Hz
Heat dissipation	3...4.5 W at 50/60 Hz

### Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
---------------------------------------	--------------------------

## Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901637769
Nbr. of units in pkg.	1
Package weight(Lbs)	0.62
Returnability	N
Country of origin	CZ

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0932 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------