



# TeSys F - contactor coil - LX1FG - 660...690 V AC 50 Hz

LX1FG660

Discontinued on: Jul 12, 2021



#### Main

Range	TeSys	
Product Or Component Type	Contactor coil	
Device Short Name	LX1FG	
Range Compatibility	TeSys TeSys F LC1F contactor	
Product Compatibility	LC1F185 LC1F225	
Control Circuit Type	AC 50 Hz	
[Uc] Control Circuit Voltage	660690 V AC 50 Hz	
Inductance Of Closed Circuit	21.8 H	
Average Resistance	154 Ohm 68 °F (20 °C)	
Operating Time	2035 ms closing 715 ms opening	
Mechanical Durability	10 Mcycles	
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)	

## Complementary

Coil Technology	Without built-in suppressor module	
Control Circuit Voltage Limits	Drop-out 0.350.55 Uc 50/60 Hz 131 °F (55 °C)) Operational 0.851.1 Uc 50/60 Hz 131 °F (55 °C))	
Inrush Power In Va	805 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))	
Hold-In Power Consumption In Va	55 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))	
Heat Dissipation	1824 W 50 Hz	

#### **Environment**

Ambient Air Temperature For Operation	23131 °F (-555 °C)
Net Weight	1.21 lb(US) (0.55 kg)

## Ordering and shipping details

Category	18401-WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
Gtin	3389110225303
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.44 in (6.2 cm)
Package 1 Width	3.11 in (7.9 cm)
Package 1 Length	6.54 in (16.6 cm)
Package 1 Weight	19.40 oz (550 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information