Product data sheet

Specifications





Standard control unit, TeSys Ultra, 1.25A to 5A, class 10, 24VDC

LUCA05BL

Product availability: Stock - Normally stocked in distribution facility

Price*: 120.00 USD

Main

Range	TeSys
Range Of Product	TeSys Ultra
Product Name	TeSys Ultra
Device Short Name	LUCA
Product Or Component Type	Standard control unit
Device Application	Motor control
	Motor protection
Product Specific Application	Basic protection requirements for motor starters: overload and short-circuit
Main Function Available	Protection against phase failure and phase imbalance
	Manual reset
	Earth fault protection
	Protection against overload and short-circuit
Product Compatibility	Power base LUB12
	Power base LUB32
	Power base LUB38
	Power base LUB120
	Power base LUB320
	Power base LUB380
	Reversing contactor breaker LU2B12BL
	Reversing contactor breaker LU2B32BL
	Reversing contactor breaker LU2B38BL
[Ue] Rated Operational Voltage	690 V AC
Network Frequency	4060 Hz
Load Type	3-phase motor self-cooled
Utilisation Category	AC-44
	AC-43
	AC-41
Motor Power Kw	1.5 kW 400440 V AC 50/60 Hz
	2.2 kW 500 V AC 50/60 Hz
	3 kW 690 V AC 50/60 Hz
Rated Motor Current Adjustment Range	1.255 A
Thermal Overload Class	Class 10 4060 Hz -13158 °F (-2570 °C) IEC 60947-6-2 Class 10 4060 Hz -13158 °F (-2570 °C) UL 508
Tripping Threshold	14.2 x lr +/- 20 %
Phase Failure Sensitivity	Yes
[Uc] Control Circuit Voltage	24 V DC

Complementary

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Control Circuit Voltage Limits	2027 V DC 24 V in operation 14.5 V DC 24 V drop-out	
Typical Current Consumption	 130 mA 24 V DC I maximum while closing with LUB12 220 mA 24 V DC I maximum while closing with LUB32 220 mA 24 V DC I maximum while closing with LUB38 60 mA 24 V DC I rms sealed with LUB12 80 mA 24 V DC I rms sealed with LUB32 80 mA 24 V DC I rms sealed with LUB38 	
Heat Dissipation	2 W control circuit with LUB12 3 W control circuit with LUB32 3 W control circuit with LUB38	
Operating Time	35 ms opening with LUB12 control circuit 35 ms opening with LUB32 control circuit 35 ms opening with LUB38 control circuit 70 ms closing with LUB12 control circuit 70 ms closing with LUB32 control circuit 70 ms closing with LUB38 control circuit	
Standards	EN 60947-6-2 IEC 60947-6-2 UL 60947-4-1, with phase barrier CSA C22.2 No 60947-4-1, with phase barrier	
Product Certifications	CE UL CSA CCC EAC ASEFA ATEX Marine	
[Ui] Rated Insulation Voltage	690 V IEC 60947-6-2 600 V UL 60947-4-1 600 V CSA C22.2 No 60947-4-1	
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-6-2	
Safe Separation Of Circuit	400 V SELV between the control and auxiliary circuits IEC 60947-1 400 V SELV between the control or auxiliary circuit and the main circuit IEC 60947-1	
Fixing Mode	Plug-in (front face)	
Width	1.77 in (45 mm)	
Height	2.60 in (66 mm)	
Depth	2.36 in (60 mm)	
Net Weight	0.30 lb(US) (0.135 kg)	
Compatibility Code	LUCA	

Environment

Ip Degree Of Protection	IP20 front panel and wired terminals IEC 60947-1 IP20 other faces IEC 60947-1 IP40 front panel outside connection zone IEC 60947-1	
Protective Treatment	TH IEC 60068	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)	
Operating Altitude	6561.68 ft (2000 m)	
Fire Resistance	1760 °F (960 °C) parts supporting live components IEC 60695-2-12 1202 °F (650 °C) IEC 60695-2-12	
Shock Resistance	10 gn power poles open IEC 60068-2-27 15 gn power poles closed IEC 60068-2-27	
Vibration Resistance	2 gn 5300 Hz power poles open IEC 60068-2-6 4 gn 5300 Hz power poles closed IEC 60068-2-6	

Resistance To Electrostatic Discharge	8 kV 3 in open air IEC 61000-4-2 8 kV 4 on contact IEC 61000-4-2
Resistance To Radiated Fields	9.14 V/m (10 V/m) 3 IEC 61000-4-3
Resistance To Fast Transients	2 kV 3 serial link IEC 61000-4-4 4 kV 4 all circuits except for serial link IEC 61000-4-4
Immunity To Radioelectric Fields	10 V IEC 61000-4-6
Immunity To Microbreaks	3 ms
Immunity To Voltage Dips	70 % / 500 ms IEC 61000-4-11

Ordering and shipping details

Category	US10I1122397
Discount Schedule	0l11
Gtin	3389110363838
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.98 in (10.100 cm)
Package 1 Width	2.17 in (5.500 cm)
Package 1 Length	3.15 in (8.000 cm)
Package 1 Weight	3.95 oz (112.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	23
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	6.24 lb(US) (2.829 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
 Rohs Exemption Information Yes
 Pvc Free
 Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information