

Product data sheet

Specifications



TeSys Integral - coil - 115...120 V AC 60 Hz

LX1LD100

⚠ Discontinued on: Dec 23, 2020

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Coil
Range Compatibility	TeSys TeSys Integral contactor breaker
Device Short Name	LX1
Control Circuit Type	AC 60 Hz
[Uc] Control Circuit Voltage	115...120 V AC 60 Hz
Average Resistance	5.89 Ohm 68 °F (20 °C)
Inductance Of Closed Circuit	1.18 H

Complementary

Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc (at <131 °F (55 °C)) Drop-out: 0.25...0.7 Uc (at <131 °F (55 °C))
Inrush Power In Va	420...500 VA 60 Hz cos phi 0.55
Hold-In Power Consumption In Va	24...36 VA 60 Hz cos phi 0.28

Environment

Net Weight	0.66 lb(US) (0.3 kg)
------------	----------------------

Ordering and shipping details

Category	22384-STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
Gtin	3389110246483
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Mercury Free	
<hr/>		
	Rohs Exemption Information	Yes
<hr/>		
<hr/>		
Eu Rohs Directive		Under investigation
<hr/>		
China Rohs Regulation		China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
<hr/>		