

Price\* : 796.00 USD

LX2FJW37 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

### Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX2FJ
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F400
Control circuit type	DC wide range
[Uc] control circuit voltage	395...439 V DC
Average resistance	9.6 Ohm at 68 °F (20 °C)
Inductance of closed circuit	0.44 H
Mechanical durability	10 Mcycles
Operating rate	<= 60 cyc/h at <= 55 °C

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.2...0.35 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Inrush power in W	290...860 W at 68 °F (20 °C)
Hold-in power consumption in W	16...47 W at 68 °F (20 °C)

### Environment

Ambient air temperature for operation	> 23...131 °F (> -5...55 °C)
Product weight	2.14 lb(US) (0.97 kg)

### Ordering and shipping details

Category	18401 - WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
Nbr. of units in pkg.	1
Package weight(Lbs)	2.1400000000000001
Returnability	N

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---