# Product data sheet

Specifications





Standard control unit, TeSys Ultra, 0.15A to 0.6A, 3P motors, thermal magnetic protection, class 10, coil 110-240VAC/DC

LUCAX6FU

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 120.00 USD

### Main

Mann	
Range	TeSys
Range Of Product	TeSys Ultra
Product Name	TeSys Ultra
Device Short Name	LUCA
Product Or Component Type	Standard control unit
Device Application	Motor control
	Motor protection
Product Specific Application	Basic protection requirements for motor starters: overload and short-circuit
Main Function Available	Protection against overload and short-circuit
	Protection against phase failure and phase imbalance
	Manual reset
	Earth fault protection
Product Compatibility	Power base LUB12
	Power base LUB32
	Power base LUB38
	Power base LUB120
	Power base LUB320
	Power base LUB380
	Reversing contactor breaker LU2B12FU
	Reversing contactor breaker LU2B32FU
	Reversing contactor breaker LU2B38FU
[Ue] Rated Operational Voltage	690 V AC
Network Frequency	4060 Hz
Load Type	3-phase motor self-cooled
Utilisation Category	AC-43
	AC-41
	AC-44
Motor Power Kw	0.09 kW 400440 V AC 50/60 Hz
Rated Motor Current Adjustment Range	0.150.6 A
Thermal Overload Class	Class 10 4060 Hz -13158 °F (-2570 °C) IEC 60947-6-2 Class 10 4060 Hz -13158 °F (-2570 °C) UL 508
Tripping Threshold	14.2 x lr +/- 20 %
Phase Failure Sensitivity	Yes
[Uc] Control Circuit Voltage	110240 V AC 110220 V DC
	110

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# Complementary

Control Circuit Voltage Limits	88264 V AC 110240 V in operation
_	88242 V DC 110220 V in operation
	55 V AC 110240 V drop-out
	55 V DC 110220 V drop-out
Typical Current Consumption	280 mA 110240 V AC I maximum while closing with LUB12
	280 mA 110240 V AC I maximum while closing with LUB32
	280 mA 110240 V AC I maximum while closing with LUB38
	280 mA 110220 V DC I maximum while closing with LUB12
	280 mA 110220 V DC I maximum while closing with LUB32
	280 mA 110220 V DC I maximum while closing with LUB38
	35 mA 110240 V AC I rms sealed with LUB12
	25 mA 110240 V AC I rms sealed with LUB32
	25 mA 110240 V AC I rms sealed with LUB38
	35 mA 110220 V DC I rms sealed with LUB12
	25 mA 110220 V DC I rms sealed with LUB32
	25 mA 110220 V DC I rms sealed with LUB38
Heat Dissipation	2 W control circuit with LUB12
Heat Blospation	3 W control circuit with LUB32
	3 W control circuit with LUB38
Operating Time	35 ms opening with LUB12 control circuit
	35 ms opening with LUB32 control circuit
	35 ms opening with LUB38 control circuit
	50 ms closing with LUB12 control circuit
	50 ms closing with LUB32 control circuit
	50 ms closing with LUB38 control circuit
Standards	EN 60947-6-2
	IEC 60947-6-2
	UL 60947-4-1, with phase barrier
	CSA C22.2 No 60947-4-1, with phase barrier
Product Certifications	CE
	UL
	CSA
	CCC
	EAC
	ASEFA
	ATEX
	Marine
[Ui] Rated Insulation Voltage	690 V IEC 60947-6-2
	600 V UL 60947-4-1
	600 V CSA C22.2 No 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-6-2
Safe Separation Of Circuit	400 V SELV between the control and auxiliary circuits IEC 60947-1
	400 V SELV between the control or auxiliary circuit and the main circuit IEC 60947-1
Fixing Mode	Plug-in (front face)
Width	1.77 in (45 mm)
Height	2.60 in (66 mm)
Depth	2.36 in (60 mm)
Net Weight	0.30 lb(US) (0.135 kg)
Compatibility Code	
Compatibility Code	LUCA

### Environment

Ip Degree Of Protection	IP20 front panel and wired terminals IEC 60947-1 IP20 other faces IEC 60947-1 IP40 front panel outside connection zone IEC 60947-1
Protective Treatment	TH IEC 60068
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)

Operating Altitude	6561.68 ft (2000 m)	
Fire Resistance	1760 °F (960 °C) parts supporting live components IEC 60695-2-12 1202 °F (650 °C) IEC 60695-2-12	
Shock Resistance	10 gn power poles open IEC 60068-2-27 15 gn power poles closed IEC 60068-2-27	
Vibration Resistance	2 gn 5300 Hz power poles open IEC 60068-2-6 4 gn 5300 Hz power poles closed IEC 60068-2-6	
Resistance To Electrostatic Discharge	8 kV 3 in open air IEC 61000-4-2 8 kV 4 on contact IEC 61000-4-2	
Non-Dissipating Shock Wave	1 kV serial mode IEC 60947-6-2 2 kV common mode IEC 60947-6-2	
Resistance To Radiated Fields	9.14 V/m (10 V/m) 3 IEC 61000-4-3	
Resistance To Fast Transients	2 kV 3 serial link IEC 61000-4-4 4 kV 4 all circuits except for serial link IEC 61000-4-4	
Immunity To Radioelectric Fields	10 V IEC 61000-4-6	
Immunity To Microbreaks	3 ms	
Immunity To Voltage Dips	70 % / 500 ms IEC 61000-4-11	

### Ordering and shipping details

Category	US10I1122397
Discount Schedule	0111
Gtin	3389110364002
Returnability	No
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.06 in (10.3 cm)
Package 1 Width	2.09 in (5.3 cm)
Package 1 Length	3.35 in (8.5 cm)
Package 1 Weight	4.41 oz (125.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	23
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	6.99 lb(US) (3.17 kg)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information