# **Product data sheet**





### Switch disconnector, MasterPact MTZ2 32HF, 3200A, 187kA/ 690VAC 50/60Hz (Icm), 3P, fixed

LV848086

#### Main

| Range                     | MasterPact            |
|---------------------------|-----------------------|
| Product Or Component Type | Switch disconnector   |
| Device Application        | Distribution          |
| Switch-Disconnector Name  | MasterPact MTZ2 32 HF |
| Poles Description         | 3P                    |
| Network Type              | AC                    |
| Network Frequency         | 50/60 Hz              |

### Complementary

| Control Type                                | Push-button  |
|---|--|
| Mounting Mode                               | Fixed  |
| [Ue] Rated Operational Voltage              | 690 V AC 50/60 Hz EN/IEC 60947-3   |
| [le] Rated Operational Current              | 3200 A AC 50/60 Hz 690 V   |
| [Ui] Rated Insulation Voltage               | 1000 V AC 50/60 Hz EN/IEC 60947-3  |
| [Uimp] Rated Impulse Withstand Voltage      | 12 kVEN/IEC 60947-3  |
| [lcw] Rated Short-Time Withstand<br>Current | 85 kA 1 s EN/IEC 60947-3<br>75 kA 3 s EN/IEC 60947-3   |
| [Icm] Rated Short-Circuit Making Capacity   | 187 kA peak 220690 V AC 50/60 Hz   |
| Utilisation Category                        | AC-23A<br>AC-3   |
| Performance Level                           | HF   |
| Suitability For Isolation                   | Yes EN/IEC 60947-3   |
| Contact Position Indicator                  | Yes  |
| Visible Break                               | No   |
| Mechanical Durability                       | 20000 cycles with periodic preventive maintenance EN/IEC 60947-3   |
| Electrical Durability                       | AC-23A 5000 cycles 440 V AC 50/60 Hz EN/IEC 60947-3<br>AC-23A 2500 cycles 690 V AC 50/60 Hz EN/IEC 60947-3 |
| Connection Pitch                            | 4.53 in (115 mm)   |
| Height                                      | 13.86 in (352 mm)  |
| Width                                       | 16.61 in (422 mm)  |
| Depth                                       | 11.81 in (300 mm)  |

#### **Environment**

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.



| Net Weight                            | 110.23 lb(US) (50 kg) |
|---------------------------------------|-----------------------|
| Standards                             | EN/IEC 60947-3        |
| Product Certifications                | IECEE CB Scheme       |
| Ip Degree Of Protection               | IP30                  |
| Pollution Degree                      | 3 EN/IEC 60947-4-1    |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C)  |
| Ambient Air Temperature For Storage   | -40185 °F (-4085 °C)  |

### Ordering and shipping details

Gtin 3606480817465

## **Packing Units**

| Unit Type Of Package 1       | PCE                     |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1                       |
| Package 1 Height             | 13.86 in (35.2 cm)      |
| Package 1 Width              | 16.61 in (42.2 cm)      |
| Package 1 Length             | 11.81 in (30.0 cm)      |
| Package 1 Weight             | 110.23 lb(US) (50.0 kg) |

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



#### **Certifications & Standards**

| California Proposition 65       | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
|---------------------------------|--|
| Circularity Profile             | End of Life Information  |
| Weee                            | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.   |
| <b>Environmental Disclosure</b> | Product Environmental Profile  |
| China Rohs Regulation           | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.   |
| Eu Rohs Directive               | Compliant with Exemptions  |
| Reach Regulation                | REACh Declaration  |