

Product data sheet

Specifications



TeSys Deca - contactor coil - LX4D7 - 125 V DC standard for 80 A contactor

LX4D7GD

⚠ Discontinued on: Jul 12, 2021

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX4D7
Control Circuit Type	DC standard
[Uc] Control Circuit Voltage	125 V DC
Inductance Of Closed Circuit	50.3 H
Product Compatibility	LC1D80
Mechanical Durability	10 Mcycles
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out: 0.1...0.3 Uc (at <131 °F (55 °C)) Operational: 0.85...1.1 Uc (at <131 °F (55 °C))
Time Constant	75 ms
Inrush Power In W	22 W 68 °F (20 °C))
Hold-In Power Consumption In W	22 W 68 °F (20 °C)

Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Net Weight	1.50 lb(US) (0.68 kg)

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	3389110209976
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------