



Price* : 134.00 USD

LX4D7WD has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Range	TeSys
Product or component type	Contacteur coil
Device short name	LX4D7
Control circuit type	DC standard
[Uc] control circuit voltage	543 V DC
Average resistance	14058 Ohm at 68 °F (20 °C)
Product compatibility	LC1D80
Mechanical durability	10 Mcycles
Operating rate	3600 cyc/h at <= 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.1...0.3 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Time constant	75 ms
Inrush power in W	22 W at 68 °F (20 °C)
Hold-in power consumption in W	22 W at 68 °F (20 °C)

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Product weight	1.5 lb(US) (0.68 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	1.5

Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1624 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------