



Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX4D8
Control circuit type	DC standard
[Uc] control circuit voltage	48 V DC
Average resistance	1061 Ohm 68 °F (20 °C)
Inductance of closed circuit	24.19 H
Product compatibility	LC1D150 LC1D115
Mechanical durability	8 Mcycles
Maximum operating rate	1200 cyc/h 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational 0.75...1.2 Uc 131 °F (55 °C) Drop-out 0.15...0.4 Uc 131 °F (55 °C)
Time constant	25 ms
Inrush power in W	270...365 W 68 °F (20 °C)
Hold-in power consumption in W	2.4...5.1 W 68 °F (20 °C)

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Net weight	0.66 lb(US) (0.3 kg)

Ordering and shipping details

GTIN	03389110868449
Package weight(Lbs)	0.66 lb(US) (0.300 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: which is known to the State of California to cause Not determined harm. For more information go to www.p65warnings.ca.gov
---------------------------	--

Contractual warranty

Warranty	18 months
----------	-----------
