



Main

Range	Masterpact
Device short name	XF diag & com
Product or component type	Voltage release
Device application	Control
Range compatibility	Masterpact MTZ2 circuit-breaker Masterpact MTZ3 circuit-breaker

Complementary

Control type	Communicating
Signalling function	Ready to close or open Coil powered Error Electrical push-button activated
[Uc] control circuit voltage	200...250 V AC 50/60 Hz 200...250 V DC
Threshold tripping voltage	0.85...1.1 Un
Hold-in power consumption in VA	4.5 VA
Supply holding power	4.5 VA
Mounting mode	Drawout
Response time	70 ms +/- 10 % Masterpact MTZ2 800 A 70 ms +/- 10 % Masterpact MTZ2 1000 A 70 ms +/- 10 % Masterpact MTZ2 1250 A 70 ms +/- 10 % Masterpact MTZ2 1600 A 70 ms +/- 10 % Masterpact MTZ2 2000 A 70 ms +/- 10 % Masterpact MTZ2 2500 A 70 ms +/- 10 % Masterpact MTZ2 3200 A 70 ms +/- 10 % Masterpact MTZ2 4000 A 70 ms +/- 10 % Masterpact MTZ3 800 A 70 ms +/- 10 % Masterpact MTZ3 1000 A 70 ms +/- 10 % Masterpact MTZ3 1250 A 70 ms +/- 10 % Masterpact MTZ3 1600 A 70 ms +/- 10 % Masterpact MTZ3 2000 A 70 ms +/- 10 % Masterpact MTZ3 2500 A

70 ms +/- 10 % Masterpact MTZ3 3200 A
70 ms +/- 10 % Masterpact MTZ3 4000 A
80 ms +/- 10 % Masterpact MTZ2 4000 A
80 ms +/- 10 % Masterpact MTZ2 5000 A
80 ms +/- 10 % Masterpact MTZ2 6300 A
80 ms +/- 10 % Masterpact MTZ3 4000 A
80 ms +/- 10 % Masterpact MTZ3 5000 A
80 ms +/- 10 % Masterpact MTZ3 6300 A

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1649 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available