

Product data sheet

Specifications



TeSys F - contactor coil - LX0FJ - 208 V AC/DC

LX0FJ020

Discontinued on: Jan 23, 2021

Discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX0FJ
Control Circuit Type	AC 50...400 Hz DC standard
[Uc] Control Circuit Voltage	208 V AC 50...400 Hz 208 V DC
Average Resistance	24.4 Ohm latching 68 °F (20 °C) 2643 Ohm unlatching 68 °F (20 °C)
Product Compatibility	CR1F400
Operating Time	50...100 ms unlatching 40...75 ms latching
Mechanical Durability	1 Mcycles
Maximum Operating Rate	120 cyc/h 104 °F (40 °C)

Complementary

Control Circuit Voltage Limits	Latching: 0.85...1.1 Uc Unlatching: 0.85...1.1 Uc
--------------------------------	--

Environment

Net Weight	2.47 lb(US) (1.12 kg)
------------	-----------------------

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	3389118109537
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months