

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 78.00 USD



### Main

Range	TeSys
Product or component type	Contacteur coil
Device short name	LX4FF
Range compatibility	TeSys F LC1F contacteur
Product compatibility	LC1F115 LC1F150
Control circuit type	DC low consumption
[Uc] control circuit voltage	440...460 V DC
Average resistance	301 Ohm inrush at 68 °F (20 °C) 48200 Ohm holding at 68 °F (20 °C)
Inductance of closed circuit	4000 H
Operating time	30...40 ms closing 30...50 ms opening
Mechanical durability	10 Mcycles
Operating rate	<= 2400 cyc/h at <= 55 °C

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.15...0.2 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Inrush power in W	560 W at 68 °F (20 °C)
Hold-in power consumption in W	4.5 W at 68 °F (20 °C)

### Environment

Ambient air temperature for operation	> 23...131 °F (> -5...55 °C)
Product weight	0.95 lb(US) (0.43 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

## Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	003389110247121
Nbr. of units in pkg.	1
Package weight(Lbs)	1.04
Returnability	N
Country of origin	CZ

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0830 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------