

# Product data sheet

Specifications



## TeSys F - contactor coil - LX4FJ - 65 V DC

LX4FJ065

! Discontinued

### Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX4FJ
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F400
Control Circuit Type	DC low consumption
[Uc] Control Circuit Voltage	65 V DC
Inductance Of Closed Circuit	270 H
Average Resistance	12.7 Ohm inrush 68 °F (20 °C) 2660 Ohm holding 68 °F (20 °C)
Operating Time	45...60 ms opening 50...60 ms closing
Mechanical Durability	10 Mcycles
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)

### Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out 0.2...0.35 Uc 131 °F (55 °C)) Operational 0.85...1.1 Uc 131 °F (55 °C))
Inrush Power In W	1000 W 68 °F (20 °C))
Hold-In Power Consumption In W	6 W 68 °F (20 °C)

### Environment

Ambient Air Temperature For Operation	23...131 °F (-5...55 °C)
Net Weight	2.14 lb(US) (0.97 kg)

### Ordering and shipping details

Category	18401-WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
Gtin	3389118114142
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Contractual warranty

Warranty	18 months
----------	-----------