



Price\*\* : 52.40 USD



ⓘ Discontinued

LX1D2R6 has not been replaced. Please contact your customer care center for more information.

## Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D2
Control circuit type	AC 60 Hz
[Uc] control circuit voltage	440 V AC 60 Hz
Average resistance	1892 Ohm at 68 °F (20 °C)
Inductance of closed circuit	71 H
Product compatibility	LC1D09...D18

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.8...1.1 Uc at <= 131 °F (55 °C) operational 60 Hz
Inrush power in VA	70 VA at 68 °F (20 °C) (cos φ 0.75) 60 Hz
Hold-in power consumption in VA	7.5 VA at 68 °F (20 °C) (cos φ 0.3) 60 Hz

## Environment

Product weight	1.54 lb(US) (0.7 kg)
----------------	----------------------

## Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901809494
Nbr. of units in pkg.	1
Package weight(Lbs)	0.17000000000000001
Returnability	N
Country of origin	FR

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0702 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------