# Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# contactor coil - LX1F - 160 V AC - 50/60 Hz



LX1FK160

### ! Discontinued

### Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1FK
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F500
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	160 V AC 50/60 Hz
Average Resistance	18.82 Ohm inrush 68 °F (20 °C) 491 Ohm holding 68 °F (20 °C)
Operating Time	100170 ms opening 4075 ms closing
Mechanical Durability	10 Mcycles
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)

### Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational 0.851.1 Uc 50/60 Hz 131 °F (55 °C)) Drop-out 0.30.5 Uc 50/60 Hz 131 °F (55 °C))

### **Environment**

Ambient Air Temperature For  $23...131~^{\circ}\text{F}~(\text{-}5...55~^{\circ}\text{C})$  Operation

## Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	112
Gtin	3389118108738
Returnability	No

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

### **Contractual warranty**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Warranty

18 months