



Price* : 144.00 USD

LX1LD048 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Range	TeSys
Product or component type	Coil
Range compatibility	TeSys Integral contactor breaker
Device short name	LX1
Control circuit type	AC 50 Hz
[Uc] control circuit voltage	48 V AC 50 Hz
Average resistance	1.26 Ohm at 68 °F (20 °C)
Inductance of closed circuit	0.29 H

Complementary

Control circuit voltage limits	0.25...0.7 Uc at <= 131 °F (55 °C) drop-out 0.85...1.1 Uc at <= 131 °F (55 °C) operational
Inrush power in VA	350...400 VA (cos φ 0.55) 50 Hz
Hold-in power consumption in VA	20...30 VA (cos φ 0.28) 50 Hz

Environment

Product weight	0.66 lb(US) (0.3 kg)
----------------	----------------------

Ordering and shipping details

Category	18402 - WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7399999999999999
Returnability	N

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0808 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------