



Price** : 483.00 USD



Main

Range	TeSys
Product or component type	Specific contactor coil
Device short name	LX9FL
Range compatibility	TeSys F LC1F contactor TeSys F DR2S resistor
Product compatibility	DR2SC LC1F630
Control circuit type	DC low consumption
[Uc] control circuit voltage	110 V AC 110 V DC
Inductance of closed circuit	0.98 H
Operating time	60 ms opening 20 ms closing
Mechanical durability	5 Mcycles
Operating rate	≤ 1800 cyc/h at ≤ 70 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.5 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Inrush power in W	733 W at 68 °F (20 °C)
Hold-in power consumption in W	48 W at 68 °F (20 °C)
Heat dissipation	22.8...27.8 W

Environment

Ambient air temperature for operation	$> 23...131$ °F ($> -5...55$ °C)
Product weight	3.2 lb(US) (1.45 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	003389110248647
Nbr. of units in pkg.	1
Package weight(Lbs)	3.3000000000000003
Returnability	N
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0915 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------