# **Product data sheet**

Specification





# motion servo drive, Lexium 28, single and three phase, 200 to 240V, 1kW

LXM28AU10M3X

Product availability: Stock - Normally stocked in distribution

acility

Price\*: 780.00 USD

#### Main

Range Of Product	Lexium 28
Product Or Component Type	Motion servo drive
Device Short Name	LXM28A
Format Of The Drive	Compact housing
Line Current	8.5 A 176.3 % 220 V, single phase 8.5 A 155.5 % 220 V, three phase

## Complementary

Phase	Single phase Three phase
[Us] Rated Supply Voltage	200240 V - 1015 %)three phase 200240 V - 2015 %)single phase
Supply Voltage Limits	200255 V three phase 170255 V single phase
Supply Frequency	50/60 Hz - 55 %
Network Frequency	47.563 Hz
Emc Filter	Without EMC filter
Continuous Output Current	7 A 16 kHz
Output Current 3S Peak	21 A 220 V
Continuous Power	1000 W 220 V
Nominal Power	1 kW 220 V 16 kHz
Switching Frequency	16 kHz
Overvoltage Category	III
Maximum Leakage Current	4.5 mA
Output Voltage	<= power supply voltage
Electrical Isolation	Between power and control
Type Of Cable	Shielded motor cable 32131 °F (055 °C)) copper
Electrical Connection	Spring terminal 1.31.5 mm², AWG 16 L1-L2) Spring terminal 1.31.5 mm², AWG 16 R, S, T) Spring terminal 1.31.5 mm², AWG 16 U, V, W, PE) Spring terminal 1.31.5 mm², AWG 16 PA/+, PBe)
Discrete Input Number	8 programmable CN1) 1 pulse train input (PTI) CN1) 2 fast capture CN1) 1 safety function STO CN9)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discrete Input Voltage	24 V DC logic
Discrete Input Logic	Positive or negative CN1)
Discrete Output Number	5 logic output CN1)1224 V DC 1 pulse train output (PTO) CN1)
Discrete Output Voltage	1224 V DC
Discrete Output Logic	Positive or negative CN1)
Analogue Input Number	2
Absolute Accuracy Error	0.1 %
Analogue Input Type	V_REF voltage analog input - 1010 V 10 kOhm 14 bits T_REF voltage analog input
Control Signal Type	Servo motor encoder feedback CN2
Protection Type	Against reverse polarity inputs signal Against short-circuits outputs signal Overcurrent motor Overvoltage motor Undervoltage motor Overheating motor Overload motor Overspeed motor
Safety Function	STO (safe torque off), Integrated
Safety Level	SIL 2 IEC 61800-5-2 2007 SIL 2 IEC 61508-1 2010 PL d/category 3 ISO 13849-1 2008 SIL 2 ISO 13849-1 2009/AC SIL 2 IEC 60204-1 2006 SIL 2 IEC 60204-1 2009/A1 SIL 2 IEC 60204-1 2010/AC SIL 2 IEC 62061 2012
Communication Interface	CANopen, Integrated CANmotion, Integrated
Connector Type	RJ45 CN4)CANopen, CANmotion
Method Of Access	Slave
Transmission Rate	250 kbit/s 328.08820.21 ft (100250 m) CANopen, CANmotion 500 kbit/s 13.12328.08 ft (4100 m) CANopen, CANmotion 1 Mbit/s 13.12 ft (4 m) CANopen, CANmotion
Number Of Addresses	1127 CANopen, CANmotion
Physical Interface	RS485 Modbus Serial line slave
Status Led	1 LED (Red) charge 1 LED (Green) RUN 1 LED (Red) error
Signalling Function	Servo status and fault codes five 7-segment display units
Marking	CE CULus CSA
Type Of Cooling	Integrated fan
Operating Position	Vertical
Product Compatibility	Servo motor BCH2 5.12 in (130 mm), 1 1000 W Servo motor BCH2 3.94 in (100 mm), 1 1000 W Servo motor BCH2 5.12 in (130 mm), 2 900 W Servo motor BCH2 5.12 in (130 mm), 4 850 W
Width	2.17 in (55 mm)
Height	5.91 in (150 mm)

Net Weight	2.65 lb(US) (1.2 kg)
Output Current 3S Peak 2	21 A 220 V
Output Current 3S Peak 3	21 A 220 V

## **Environment**

Electromagnetic Compatibility	Conducted emission - test level: level 3 category C3 conforming to IEC 61800-3
Standards	IEC 61800-5-1
Product Certifications	CE
	CSA
	cULus
Ip Degree Of Protection	IP20
Vibration Resistance	3M4 3 mm 9200 Hz)IEC 60721-3-3
Shock Resistance	10 gn, type I IEC 60721-3-3
Relative Humidity	595 % without condensation
Ambient Air Temperature For Operation	32131 °F (055 °C)
Ambient Air Temperature For Storage	-13149 °F (-2565 °C)
Operating Altitude	<= 3280.84 ft (1000 m) without derating
	> 3280.846561.68 ft (> 10002000 m) 1 % per 100 m

# Ordering and shipping details

Category	US1PC5118262
Discount Schedule	PC51
Gtin	3606480711800
Returnability	Yes
Country Of Origin	CN

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.97 in (7.555 cm)
Package 1 Width	9.01 in (22.89 cm)
Package 1 Length	9.35 in (23.756 cm)
Package 1 Weight	3.31 lb(US) (1.5 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	5
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	18.49 lb(US) (8.387 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


## **Product data sheet**

### LXM28AU10M3X

**Dimensions Drawings** 

#### **Dimensions**

#### **Dimensions of Drive**



#### LXM28AU10M3X

Mounting and Clearance

#### **Mounting Clearance**

#### **Mounting Distances and Air Circulation**

mm

