

Product data sheet

Characteristics

LX4D7XD

TeSys D - contactor coil - LX4D7 - 600 V DC
standard for 80 A contactor

Product availability : Non-Stock - Not normally stocked in distribution facility

Price** : 140.70 USD



Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX4D7
Control circuit type	DC standard
[Uc] control circuit voltage	600 V DC
Average resistance	17425 Ohm 68 °F (20 °C)
Product compatibility	LC1D80
Mechanical durability	10 Mcycles
Maximum operating rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.1...0.3 Uc 131 °F (55 °C) Operational 0.85...1.1 Uc 131 °F (55 °C)
Time constant	75 ms
Inrush power in W	22 W 68 °F (20 °C)
Hold-in power consumption in W	22 W 68 °F (20 °C)

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Net weight	1.50 lb(US) (0.68 kg)

Ordering and shipping details

Category	18401 - WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
GTIN	03389110190373
Package weight(Lbs)	0.68 kg (1.5 lb(US))
Returnability	No
Country of origin	CZ

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------