


Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 394.00 USD



### Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX4FH
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F265 LC1F330
Control circuit type	DC wide range
[Uc] control circuit voltage	72 V DC
Average resistance	5.58 Ohm inrush 68 °F (20 °C) 1110 Ohm holding 68 °F (20 °C)
Inductance of closed circuit	149 H
Operating time	40...50 ms closing 40...65 ms opening
Mechanical durability	10 Mcycles
Maximum operating rate	60 cyc/h 131 °F (55 °C)

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational 0.85...1.1 Uc 131 °F (55 °C) Drop-out 0.15...0.2 Uc 131 °F (55 °C)
Inrush power in W	750 W 68 °F (20 °C)
Hold-in power consumption in W	5 W 68 °F (20 °C)

### Environment

Ambient air temperature for operation	23...131 °F (-5...55 °C)
Net weight	1.63 lb(US) (0.74 kg)

## Ordering and shipping details

Category	18401 - WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
GTIN	03389110247183
Package weight(Lbs)	0.88 kg (1.94 lb(US))
Returnability	No
Country of origin	CZ

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: No which is known to the State of California to cause No harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------