




Price** : 394.00 USD

LX4FH250 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX4FH
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F330 LC1F265
Control circuit type	DC low consumption
[Uc] control circuit voltage	250 V DC
Average resistance	84 Ohm inrush 68 °F (20 °C) 13900 Ohm holding 68 °F (20 °C)
Inductance of closed circuit	1910 H
Operating time	40...50 ms closing 40...65 ms opening
Mechanical durability	10 Mcycles
Maximum operating rate	2400 cyc/h 131 °F (55 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational 0.85...1.1 Uc 131 °F (55 °C) Drop-out 0.15...0.2 Uc 131 °F (55 °C)
Inrush power in W	750 W 68 °F (20 °C)
Hold-in power consumption in W	5 W 68 °F (20 °C)

Environment

Ambient air temperature for operation	23...131 °F (-5...55 °C)
Net weight	1.63 lb(US) (0.74 kg)

Ordering and shipping details

Category	18401-WORLD SERVICE PARTS(CTR ACCESS)
----------	---------------------------------------

Discount Schedule	CP10
GTIN	03389110247190
Package weight(Lbs)	1.83 lb(US) (0.830 kg)
Returnability	No

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: which is known to the State of California to cause Not determined harm. For more information go to www.p65warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------